

YSD26R26R

by Burndy
Catalog ID: YSD26R26R

Prop 65 Notice

AL compression sleeve with solid center barrier, Designed for commercial and heavy residential services, Color Code: Gray (Side A), Gray (Side B).

Features: Aluminum Compression Sleeve With Solid Center Barrier, Designed For Commercial And Heavy Residential Services, Installed With Standard Tooling, Pre-Filled With PENETROX, Joint Compound, And Capped, Die Index: 249 Element A, Conductor Type: Side A And Side B: ACSR, Aluminum, Copper, Aluminum Compact 6201, 5005, Tools, Die Set Catalog Number, And (number Of Crimps): HYTOOL: MD6 Tool, WK-840 Die, (7), MD7 Tool, W-249 Die, (4), OUR840 Tool, X840 Die, (7), X249 Die, (8), HYPRESS: Y35, Y750 Tool, UK840 Die, (4), Y35, Y750 Tool, U249 Die, (2), Color Code: Gray (Side A And B)



Product Details

General

Application	For Combinations Of Copper, Aluminum, ACSR, 6201, 5005 and Compressed Conductors
Color Code - Side A	Gray
Color Code - Side B	Gray
Die Index	249;K-840
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	LINKIT
Trade Name	LINKIT™
Type	Service Entrance, Uninsulated
UPC	781810144206
UPC 12 Digit	7818101442066

Dimensions

Dimension - L Length Overall mm	102 mm
Dimension - Length Overall inch	4 in
Dimension - Outside Diameter inch	.3125 in

Conductor Related

Conductor - ACSR Str Size A	2/0 (6/1) Quail AWG
Conductor - ACSR Str Size B	2/0 (6/1) Quail AWG
Conductor - AL Str Size A	2/0 AWG
Conductor - AL Str Size B	2/0 AWG
Conductor - Copper Str Size A	2/0 AWG
Conductor - Copper Str Size B	2/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)