

YST3434

by Burndy
Catalog ID: YST3434

Prop 65 Notice

Cu compression T-Coupler, 500Kcmil(Run),500Kcmil(Tap),
Brown(Run&Tap), 20(Run&Tap) Index.

Features: Manufactured from seamless high conductivity electrolytic
copper, Electro-tin plated



Product Details

General

Application	Used in junction boxes and manholes
Color Code	Brown
Color Code - Side A	Brown
Color Code - Side B	Brown
Connector Type	Tap
Die Index	299;20
Die Index Run Side	20
Die Index Tap Side	20
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYTEE
Temperature Rating	194
Trade Name	HYTEE™
Type	YST, Uninsulated T
UPC	781810502075
UPC 12 Digit	7818105020755

Dimensions

Dimension - A Outside Diameter inch	1.06 in
Dimension - B Length fraction	2-1/4 in
Dimension - B Length inch	2.25 in
Dimension - B Outside Diameter inch	1.06 in
Dimension - Height inch	3.76 in
Dimension - L Length Overall mm	157 mm
Dimension - Length BB inch	2.70 in
Dimension - Length Overall inch	6.19 in
Dimension - Width inch	2.60 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Run	500 kcmil
Conductor - Copper Str Run Range	500 kcmil
Conductor - Copper Str Tap	500 kcmil
Conductor - Copper Str Tap Range	500 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)