



YTS431A

by Burndy
Catalog ID: YTS431A

Prop 65 Notice

Al Tube Full Tension Splice, 874.5, 954 kcmil Al, 230 kV, 16.51" L, 725 Index

Product Details

General

| | |
|---------------------------|---------------|
| Connector Type | Splice |
| Die Index | 725 |
| Material | Aluminum |
| Plated | N |
| Plating Type | Unplated |
| Prefilled Oxide Inhibitor | Y |
| Trade Name | HYSPLICE™ |
| UPC | 781810016312 |
| UPC 12 Digit | 7818100163122 |

Dimensions

| | |
|---------------------------------|----------|
| Dimension - L Length Overall mm | 419 mm |
| Dimension - Length Overall inch | 16.51 in |

Conductor Related

| | |
|-------------------------|--|
| Conductor - AL Str Size | 874.5 (37, 61) Kcmil; 954 (37, 61) Kcmil |
|-------------------------|--|

Certifications and Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)