

YTS451AR

by Burndy
Catalog ID: YTS451AR

Prop 65 Notice

Al Tubing Full Tension Splice, 840.2, 853.7, 862.7, 927.2 kcmil ACAR,
19.50" L, 725 Index



Product Details

General

Connector Type	Splice
Die Index	725
Material	Aluminum
Prefilled Oxide Inhibitor	Y
Trade Name	HYSPLICE™
UPC	781810016237
UPC 12 Digit	7818100162377

Dimensions

Dimension - L Length Overall mm	497 mm
Dimension - Length Overall inch	19.58 in

Conductor Related

Conductor - ACAR Str Size	840.2 Kcmil; 853.7 Kcmil; 862.7 Kcmil; 927.2 Kcmil
---------------------------	--

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)