

YTS451RT

by Burndy
Catalog ID: YTS451RT

Prop 65 Notice

Al Sleeve for Full tension Splice Kit, Length: 28.96 IN, Die Index: 725



Product Details

General

Connector Type	Splice
Material	Aluminum
Trade Name	HYSPLICE™
UPC	781810016503
UPC 12 Digit	7818100165033

Dimensions

Dimension - L Length Overall mm	28.96 mm
Dimension - Length Overall inch	735.6 in

Conductor Related

Conductor - ACSR Str Size	715.5 (26/7) Starling Kcmil; 715.5 (54/7) Crow Kcmil; 795 (24/7) Cuckoo Kcmil; 795 (26/7) Drake Kcmil; 795 (45/7) Tern Kcmil; 795 (54/7) Condor Kcmil
---------------------------	---

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)