



BURNDY Catalog Number
UPC Number

CT120300SSBL
7818106431299
120LB SSB NYLON CT, NATURAL
COLOR
Active

Description
Status

Web Use
BURNDY Product Line

Dimensional

Width (in)	0.39
Width (mm)	10
Length (in)	11.81
Length (mm)	300

General

Product Description
Nylon Stainless Steel BARB Cable
Ties, 11.81 IN L, .39 IN W, Tensile
Strength: 120 Lbs, Max bundle
dia:3.15"

Approvals / Certifications

ROHS Compatible	Compliant
CULUS	Y

Physical

Max. Bundle Diameter (in)	3.15
Color	Natural

Mechanical

Min Tensile Strength (lbs)	120
----------------------------	-----

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175