



**BURNDY Catalog Number**  
**UPC Number**  
**Description**  
**Status**

NAH3434N  
7818100022477  
TERM.FOR CU RANGE TAKING  
Active

**Web Use**  
BURNDY Product Line

	<b>Dimensional</b>
Pad Orientation	0°
Width (in)	2.56
Length (in)	5.88
Thickness (in)	1/4
Height (in)	2.38
Size (Hex) or Size (Bolt)	1/2
Hole Size (Fraction)	9/16
Thickness	0.25
Size (Hex) or Size (Bolt) - in	0.50
B Length (in)	2.62
Pad Width (in)	3.00
E - in	1.75

Number of Conductors  
Product Description

**General**  
1  
Cast Copper alloy terminal, 1/0  
Sol.-500 kcmil, Cable to Pad

Copper Solid Size (Range)  
Copper Stranded (Range)

**Conductor(s)**  
1/0 AWG-4/0 AWG  
1/0 -500 kcmil

Type of Hardware  
Pad Configuration  
Type of Plating  
Connector Type  
Plated (Yes or No)  
Product Material

**Physical**  
DURIUM& Silicon Bronze  
3 x 3 - 4 holes  
Unplated  
Terminal  
N  
Copper Alloy

UL Listed  
CSA Certified  
ROHS Compatible  
UL Recognized  
CULUS

**Approvals / Certifications**

N  
N  
Exempt  
N  
N

**Documentation**

**For further technical assistance, please contact us**

**BURNDY LLC - USA**

47 East Industrial Park Drive  
Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
Monday - Friday  
Phone: 800-346-4175