



**BURNDY Catalog Number**  
**UPC Number**  
**Description**  
**Status**

NAR45A4N  
 7818100038933  
 AL TERM 900-1250  
 Active

**Web Use**  
 BURNDY Product Line

Bolt Size as a fraction  
 Length (in)  
 Height (in)  
 Size (Hex) or Size (Bolt)  
 Thickness  
 Size (Hex) or Size (Bolt) - in  
 D - in  
 Pad Width (in)  
 Pad Alignment  
 E - in  
 Pad Orientation

**Dimensional**

1/2  
 7.12  
 3.31  
 1/2  
 0.50  
 0.50  
 3.00  
 3.00  
 Offset  
 1.75  
 0°

KV Rating

**Electrical**

230

Number of Conductors  
 Number of Holes

**General**

1  
 4

Product Description

Al Bolted Terminal, Connection Type: Cable to Pad, Al Str. Range: 900-1250 Kcmil, Al. ACSR: 715.5-1113 Kcmil, Pad width: 3 IN

**Conductor(s)**

ACSR Size (Range)  
 Aluminum Size (Range)

715.5 (30/19) Redwing kcmil-1113 (54/19) Finch kcmil  
 900 kcmil-1250 kcmil

Installation Torque  
 Pad Configuration  
 Type of Plating  
 Connector Type  
 Plated (Yes or No)  
 Product Material

**Physical**

300  
 3 x 3 - 4 holes  
 Unplated  
 Terminal  
 N  
 Aluminum Alloy

**Approvals / Certifications**

UL Listed  
 CSA Certified  
 ROHS Compatible  
 UL Recognized  
 CULUS

N  
 N  
 Compliant  
 N  
 N

**Documentation**

**For further technical assistance, please contact us**

**BURNDY LLC - USA**

47 East Industrial Park Drive  
 Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM

Monday - Friday  
 Phone: 800-346-4175