



YAV10L36NK

by Burndy
Catalog ID: YAV10L36NK

Prop 65 Notice

LARGE SIZE UNINSULATED COMPRESSION TERMINALS SEAMLESS
UNINSULATED COMPRESSION RING TONGUE TERMINAL.

Product Details

General

Connector Type	Terminal
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Nickel
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810086070
UPC 12 Digit	7818100860700

Dimensions

Dimension - Length Overall inch	0.86 in
Dimension - Pad Width inch	0.29 in
Dimension - Stud Size inch	#8;#10
Dimension - Z inch	0.23 in

Conductor Related

Conductor - Copper Solid Size	12 AWG;11 AWG;10 AWG
Conductor - Copper Solid Size Range	12 AWG-10 AWG
Conductor - Copper Str Size	12 AWG;10 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size • CU C Str Aircraft-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467

Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	200
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)