

YAV14NK

by Burndy
Catalog ID: YAV14NK

Prop 65 Notice

SEAMLESS UNINSULATED COMPRESSION HEAVY DUTY RING TONGUE TERMINAL.



Product Details

General

Connector Type	Terminal
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Nickel
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810034279
UPC 12 Digit	7818100342799

Dimensions

Dimension - Length Overall inch	0.78 in
Dimension - Pad Width inch	0.29 in
Dimension - Stud Size inch	#8;#10
Dimension - Z inch	0.24 in

Conductor Related

Conductor - Copper Str Size	20 AWG;18 AWG;16 AWG;14 AWG
Conductor - Copper Str Size Range	20 AWG-14 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM

UL Listed

No

Logistics

Minimum Pack Quantity

1000

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)