



YAV6CL2NT10E2FX

by Burndy
Catalog ID: YAV6CL2NT10E2FX

Prop 65 Notice

Copper Tubing Compression Terminal, 2 Holes W/insp Window, Flex: #6 Weld (61/24), Code: #6 AWG, 30 Navy, 2.06 IN L, .44 IN W, 7 or 374 Index, #10 Bolt

Product Details

General

Color Code	Blue
Connector Type	Terminal
Die Index	7;374
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810485187
UPC 12 Digit	7818104851877

Dimensions

Dimension - B Length fraction	1/2 in
Dimension - B Length inch	0.50 in
Dimension - Bolt Hole Size inch	0.20 in
Dimension - Hole Size inch	0.20 in
Dimension - Hole Size mm	5 mm
Dimension - L Length Overall mm	52 mm
Dimension - Length Overall inch	2.06 in
Dimension - N inch	0.25 in
Dimension - Outside Diameter inch	0.31 in
Dimension - Pad Width inch	0.44 in
Dimension - Strip Length inch	9/16 in
Dimension - Z inch	0.26 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	6 (61/24) DLO
Conductor - Copper DLO Size Range	6 (61/24) DLO
Conductor - Copper Flex G Size	6 AWG
Conductor - Copper Flex G Size Range	6 AWG
Conductor - Copper Flex H Size	6 AWG
Conductor - Copper Flex H Size Range	6 AWG
Conductor - Copper Flex I Size	6 AWG
Conductor - Copper Flex I Size Range	6 AWG
Conductor - Copper Flex K Size	6 AWG
Conductor - Copper Flex K Size Range	6 AWG
Conductor - Copper Flex M Size	6 AWG
Conductor - Copper Flex M Size Range	6 AWG
Conductor - Copper Solid Size	6 AWG
Conductor - Copper Solid Size Range	6 AWG
Conductor - Copper Str Navy Size	30 Navy
Conductor - Copper Str Navy Size Range	30 Navy
Conductor - Copper Str Size	6 AWG
Conductor - Copper Str Size Range	6 AWG
Conductor - CopperWeld Str Size	#6 WELD (61/24)
Conductor - CopperWeld Str Size Range	#6 WELD (61/24)
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	50
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)