

CROSS REFERENCE GUIDE

FUSE	VOLT	EDISON	BRUSH	OLD RELIANCE/ BRUSH	GEC/CEFCO	GOULD	IR	FERRAZ	FUSETEK	LITTELFUSE	
<b>SEMICONDUCTOR FUSES</b>											
U.S.A. Dimensions	130/150	E13S, E15SF, E15S	XL-SF13X	RFA	CSF-15X	A13X	SF13X	A013FA	RF13X	L15S, KLW, KLA	
	250	E25S, E25SF	XL25X	RFN	CSF25X	A25X	SF25X	A025FA	RF25X	L25S, KLB	
	500	E50S, E50SF	XL50F	RFV	CSF50P	A50P	SF50P	A050FA	RF50X	L50S, KLH	
	600	E60S, E60SF	XL60X	RFS	CSF60X	A60X	SF60X	A060FA	RF60X	L60S	
	600	E60C	XL60C	RFC	—	A60X-4K	SF60C	—	—	—	
	700	E70S, E70SF	XL70F	RFL	CSF70P	A70P	SF70P	A070FA	RF70P	L70S	
	1000	E100S, E100SF	XL100P	RFK	CSF100P	A100P	SF100P	A070FB	RF100P	—	
European Dimensions	240	LCT	LCT	—	GSA	—	A350	—	URE	—	
		LET	LET	—	GSA & GSD	—	L350	—	URGS	—	
		LMT	LMT	—	GSA & GSD	—	T350	—	URGGT	—	
		LMMT	LMMT	—	GSA & GSD	—	TT350	—	URGHT	—	
	660	FC	CT, FC	—	GSB	—	B1000	—	6.6URE	—	
		FE	ET, FE	—	GSB	—	E100	—	6.6URS	—	
	FEE, EET	EET, FEE	—	GSGB	—	EE1000	—	6.6URT	—		
	FM	MT, FM	—	GSB, GSGB	—	M1000	—	6.6URGLT	—		
	FMM	MMT, FMM	—	GSB, GSGB	—	MM1000	—	6.6URGMT	—		
Trip Indicators	500	TI500	TI500	—	GS700	—	I700	—	—	—	
	700	TI700	TI700	—	CSL1000	—	I1000	—	—	—	

KV	BODIES	EDISON	BRUSH	GOULD	GE	CGE	WESTING- HOUSE	WESTING- HOUSE	GEC/CEFCO	NELSON	CHAMBERS	FUSETEK
----	--------	--------	-------	-------	----	-----	-------------------	-------------------	-----------	--------	----------	---------

**MEDIUM VOLTAGE "R" RATED MOTOR CIRCUIT FUSES**

4.8/ 5.5	1	5.5VFNHA2R	5.5VFNHA2R	A480-2R	9F60LJD802	328L493G14	151D241G02	208D512G02	5.5KDAX2R	70-2M-1C-5.5	48-FM-2X-4	MRP1.2R
	1	5.5VFNHA3R	5.5VFNHA3R	A480-3R	9F60LJD803	328L493G16	151D241G03	208D512G03	5.5KDAX3R	100-3M-1C-5.5	48-FM-3X-4	MRP1.3R
	1	5.5VFNHA4R	5.5VFNHA4R	A480-4R	9F60LJD804	328L493G17	151D241G04	208D512G04	5.5KDAX4R	130-4M-1C-5.5	48-FM-4X-4	MRP1.4R
	1	5.5VFNHA6R	5.5VFNHA6R	A480-6R	9F60LJD806	328L493G19	151D241G06	208D512G06	5.5KDAX6R	170-6M-1C-5.5	48-FM-6X-4	MRP1.6R
	1	5.5VFNHA9R	5.5VFNHA9R	A480-9R	9F60LJD809	328L493G21	151D961G01	208D522G01	5.5KDAX9R	200-9M-1C-5.5	48-FM-9X-4	MRP1.9R
	1	5.5VFNHA12R	5.5VFNHA12R	A480-12R	9F60LJD812	328L493G23	151D961G02	208D522G02	5.5KDAX12R	230-12M-1C-5.5	48-FM-12X-4	MRP1.12R
2.4/ 2.75	2	5.5VFNHK18R	5.5VFNHK18R	A480-18R	9F60MJD818	328L493G25	151D961G03	208D522G02	5.5KDBX18R	390-18M-2C-5.5	48-FM-18X-5	MRP1.18R
	2	5.5VFNHK24R	5.5VFNHK24R	A480-24R	9F60MJD824	328L493G27	151D961G04	208D522G03	5.5KDBX24R	450-24M-2C-5.5	48-FM-24X-5	MRP1.24R
	1	2.75VFRHA2R	2.75VFRHA2R	A240-2R	9F60LCB802	328L492G14	591C812G02	208D480G02	—	70-2M-1C-2.75	24-FM-2X-4	FC6005.2R
	1	2.75VFRHA3R	2.75VFRHA3R	A240-3R	9F60LCB803	328L492G16	591C812G03	208D480G03	—	100-3M-1C-2.75	24-FM-3X-4	FC6005.3R
	1	2.75VFRHA4R	2.75VFRHA4R	A240-4R	9F60LCB804	328L492G17	591C812G04	208D480G04	—	130-4M-1C-2.75	24-FM-4X-4	FC6005.4R
	1	2.75VFRHA6R	2.75VFRHA6R	A240-6R	9F60LCB806	328L492G19	591C812G06	208D480G06	—	170-6M-1C-2.75	24-FM-6X-4	FC6005.6R
1	2.75VFRHA9R	2.75VFRHA9R	A240-9R	9F60LCB809	328L492G21	591C812G07	208D480G07	—	200-9M-1C-2.75	24-FM-9X-4	FC6005.9R	
1	2.75VFRHA12R	2.75VFRHA12R	A240-12R	9F60LCB812	328L492G23	591C812G08	208D480G08	—	230-12M-1C-2.75	24-FM-12X-4	FC6005.12R	
2	2.75VFRHK18R	2.75VFRHK18R	A240-18R	9F60MCB818	328L492G25	591C812G01	208D480G09	—	390-18M-2C-2.75	24-FM-18X-5	FC6005.18R	
2	2.75VFRHK24R	2.75VFRHK24R	A240-24R	9F60MCB824	328L492G27	591C812G02	208D480G10	—	450-24M-2C-2.75	24-FM-24X-5	—	

KV	BODY LENGTH	AMPS	EDISON	GEC	B & S	DELLE
----	----------------	------	--------	-----	-------	-------

**H.V. DIN DISTRIBUTION FUSES**

3.6	292mm	6-40	3.6ADLSJ	—	SOLDD	—
		50-125	3.6WDLSJ	—	SOLDD	—
		160-200	3.6WFLSJ	—	SRLDD	—
		250-400	3.6WKLSJ	—	SRLDD	—
7.2	292mm	6-31	7.2SDLSJ	DSSAX	SOLDD	FD3
		40-63	7.2SDLSJ	DSSAX	SRLDD	FD3
		180-100	7.2SFLSJ	DSSAX	SRLDD	FD3
		125-160	7.2SFLSJ	DSSBX	SRLDD	—
		200-355	7.2WKMSJ	DSL BX	SRMDD	—
12	292mm	6-50	12SDLSJ	DESAGX	—	FD4
		50-80	12SFLSJ	DESAX	—	FD4
		100	12SDLSJ	DESBX	—	—
		125	12SKLSJ	—	—	—
		292mm	6-25	17.5SDLSJ	—	SOLDD
17.5	442mm	31-50	17.5SFLSJ	—	SFLDD	—
		6-40	17.5SDMSJ	DFLAX	SOMDD	FD5
		40-63	17.5SFMSJ	DFLAX	SRMDD	FD5
15.5	442mm	80	17.5SFMSJ	DFLBX	SRMDD	—
		100-125	15.5SFMSJ	DFLBX	—	—
25	442mm	6-31	24SDMSJ	DTLAX	—	FD6
		40-50	24SFMSJ	DTLAX	—	FD6
		63-71	24SFMSJ	DTLBX	—	FD6
36	537mm	3-25	36SDQSJ	DHMBX	—	FD7
		31-56	36SFQSJ	BHMBX	—	FD7