



Eaton Bussmann series 8HLE fuse

8HLE-25E

UPC:786670600329

Dimensions:

- **Height:** 3 IN
- **Length:** 15.9 IN
- **Width:** 3 IN

Weight:.001 LB

Notes:Consult factory for mountings.

Warranties:

- Not Applicable

Specifications:

- **Type:** E-Rated power
- **Special Features:** Indoor/outdoor, single barrel
- **Application:** Indoor / Outdoor
- **Voltage Rating:** 7.2 kV
- **Amperage Rating:** 25A
- **Interrupt Rating:** 50 kAIC
- **Class:** Class E
- **Diameter:** 3 IN
- **Barrels:** Single barrel
- **Maximum Voltage:** 8.3 kV
- **Series:** HLE

Supporting documents:

- [Medium voltage power fuses](#)
- [Eatons Volume 14-Fuses](#)
- [Product Catalog](#)
- [Eaton Specification Sheet - 8HLE-25E](#)

Certifications:

- IEEE Std. C37.41
- Not Applicable

Product compliance:

- Contact Manufacturer

© 2016 Eaton. All rights reserved.