

Weatherproof Non-Metallic Covers

Single-Gang — Vertical Mount

- For use in wet/damp locations
- Mounts to a box or device
- Non-metallic — won't rust or fade
- Paintable
- Easy to install
- Made in the U.S.A.



Duplex Receptacle



CAT. NO.	COLOR	STD. CTN.	STD. WT. (LBS.)
E98GDRN-CAR	Gray	10	2

GFCI Receptacle

- Device opening dimensions: 2.63" H x 1.31" W



CAT. NO.	COLOR	STD. CTN.	STD. WT. (LBS.)
E98GFCN-CAR	Gray	10	2

15-Amp Receptacle

- For 15-Amp or other single receptacles under 1.375" diameter



CAT. NO.	COLOR	STD. CTN.	STD. WT. (LBS.)
E98SRCN-CAR	Gray	10	2.1

20-Amp Receptacle

- For 20-Amp or other single receptacles under 1.625" diameter



CAT. NO.	COLOR	STD. CTN.	STD. WT. (LBS.)
E98G20N	Gray	20	4.1

30-Amp Receptacle

- For 30-Amp or other single receptacles under 1.750" diameter



CAT. NO.	COLOR	STD. CTN.	STD. WT. (LBS.)
E98G30N-CAR	Gray	10	2.1

Single Switch



CAT. NO.	COLOR	STD. CTN.	STD. WT. (LBS.)
E98SSCN-CAR	Gray	10	2.1

Toggle Switch



CAT. NO.	COLOR	STD. CTN.	STD. WT. (LBS.)
E98TSCN-CAR	Gray	5	1.1

Blank

- Supplied with stainless steel mounting screws and gasket



CAT. NO.	COLOR	STD. CTN.	STD. WT. (LBS.)
E980CN-CAR	Gray	12	1.60
E980CM-CAR	White	12	1.60

50-Amp Receptacle

- For 50-Amp or other single receptacles under 2.250" diameter



CAT. NO.	COLOR	STD. CTN.	STD. WT. (LBS.)
E98G5FN-CAR	Gray	10	2