



Actual

Catalog Number: 12007-025
Product ID: 7TAA234980R0001
UPC Number: 03448119490
Status: A

ENT Flexible Raceway, Size 3/4 Inch, Nominal Inner Diameter 0.76 Inches, Nominal Outer Diameter 1.05 Inches, Minimum Bend Radius 6 Inches, Color Blue, Length 25 Feet

- One piece ENT coupling, threaded terminator and rigid non-metallic conduit fittings are rated concrete tight without tape.
- Lightweight, hand bendable, and free from sharp edges which reduces installation time and saves money.

North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5535 Electrical conduit
Type	ENT Flexible Raceway
Special Features	Recognized for use with PVC rigid non-metallic conduit fittings with all size of ENT.
Application	Flex-Plus Blue ENT is a non-metallic flexible raceway for use in walls, floors, and non-plenum ceilings.
Standard	UL E73317
Trade Size	3/4 Inch
Outside Diameter	1.05 in
Inside Diameter	0.76 in
Length	25 ft
Material	Non-Metallic
Color	Blue

European Specifications (ETIM)

ETIM	EC001175 Corrugated plastic hose
Nominal diameter	19.05mm
Nominal size in inch	3/4 inch
Outer diameter	26.67mm
Inner diameter	19.304mm
Material	PVC
Colour	Blue
Sheathing material	Not sheathed
Approved according to DIN EN 61386-23	N
Approved according to UR	N
Approved according to LUL/British Standard	N
Approved according to Lloyd's Register TA	N
Approved according to UTAC	N
Approved according to DIN 5510	N
Approved according to NF F 16-101	N

Packaging

Outer Quantity	25
Outer Dimensions (inches)	24x16x15.125
Weight Uom	15.88 lbs. per 100

Documents / Support Tools

Support/Tools	Available on Website
---------------	----------------------