



Actual

Catalog Number: LT20G
Product ID: 7TAD012890R0007
UPC Number: 03448108515
EAN Number: 05415022442267
Status: Active

1-1/4 Inch, 90 Degree, Two-Piece Liquidtight Non-Metallic Fitting, UL E32447, Temperatures up to 107 Degrees C, Nitril Rubber O-Ring, PVC, Grey

- Non-conductive and non-corrosive.
- Resistant to oil, acid, ozone and alkaline.
- Easy to install.
- Approved for indoor and outdoor locations
- UL listed for wet locations
- Nitrile rubber 'O' ring for a liquidtight termination.
- Temperatures up to 225 degree F (107 degree C)
- Meets UL standard 514B.

North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Brand Name	Carlton
Type	Liquidtight Fittings
Application	For use with Carflex conduit and Carflex X-Flex conduit.
Standard	cULus
Size	1-1/4 Inch
Material	Non-Metallic

European Specifications (ETIM)

ETIM	EC001178 Screw connection for protective plastic hose
Nominal size in inch	1 1/4 inch
Model	90°-elbow
Revolving thread	N
Construction type	External thread
Type of connection	Thread
Thread connection size	Other
Thread length	19.05mm
One-piece	N
Material screw gland	Other
Colour	Grey

Packaging

Outer Quantity	5
Outer Dimensions (inches)	2.9x12x5.9
Weight Uom	30 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-AC03583
Technical Drawing / Data Sheet Canada	Available on Website

For further technical assistance, please contact us...

860 Ridge Lake Blvd.
Memphis, TN 38120
www.tnb.com

MS 3B-50
860 Ridge Lake Blvd.
Memphis, TN 38120

Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com