



Actual

Catalog Number: LN20DA
Product ID: 7TAD012890R0001
UPC Number: 03448104395
EAN Number: 05415022248562
Status: Active

1/2 Inch, 90 Degree, One-Piece Liquidtight Non-Metallic Fitting, CSA, UL E32447, Temperatures up to 60 Degrees C, PVC, Grey

- Unique design, the simple one-piece body requires no disassembly of components for installation. The system is so strong that there is no need for a compression nut.
- PVC construction of the fitting and locknut provides unparalleled protection from water, oil and dust.
- Non-conductive and will not corrode or rust.
- Temperatures up to 140 degree F (60 degree C)

North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Brand Name	Carlton
Type	Liquidtight Fittings
Standard	UL E23018, CSA
Size	1/2 Inch
Material	Non-Metallic

European Specifications (ETIM)

ETIM	EC001178 Screw connection for protective plastic hose
Nominal size in inch	1/2 inch
Model	90°-elbow
Revolving thread	N
Construction type	External thread
Type of connection	Plug-in connection
Thread length	14.22mm
One-piece	Y
Material screw gland	Other
Colour	Grey

Packaging

Outer Quantity	100
Outer Dimensions (inches)	11.4x7.6x5.5
Weight Uom	0.04 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-AC00828
Technical Drawing / Data Sheet Canada	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
www.tnb.com

T&B Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com