



Actual

Catalog Number: LT938
Product ID: 7TAD012910R0031
UPC Number: 03448115207
Status: Active

3/8 Inch 90 Degree Black Liquidtight Non-metallic Omni Connector

North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Brand Name	Carlton
Type	Omni Connectors
Special Features	No Disassembly Required.
Application	Suitable for Indoor/outdoor Use.
Standard	UL E23018
Material	Non-Metallic
Color	Black

European Specifications (ETIM)

ETIM	EC001178 Screw connection for protective plastic hose
Nominal size in inch	3/8 inch
Degree of protection (IP)	IP68
Model	90°-elbow
Revolving thread	N
Construction type	External thread
Type of connection	Plug-in connection
Thread connection size	Other
Thread length	13.2mm
One-piece	Y
Material screw gland	Polyamide
Colour	Black

Packaging

Inner Quantity	25
Inner Dimensions (inches)	6.375x6.375x6.75
Outer Quantity	200
Outer Dimensions (inches)	14.25x14.25x14.75
Weight Uom	0.07 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-AC03717
--------------------------------	-------------

For further technical assistance, please contact us...

Thomas & Betts - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
www.tnb.com

T&B Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com