



Actual

**Catalog Number:** FN-426-C-V  
**Product ID:** 7TAA040250R0005  
**UPC Number:** 78635800428  
**Status:** Active

Ceiling Fixture Vapor-Tight Box, Volume 26 Cubic Inches, Length 4 Inches, Width 4 Inches, Depth 2-3/4 Inches, Color Black, Material Polycarbonate, Mounting Means Angled Side Nails

- Will not shatter when cold or distort in heat
- 1/2 Inch offset flange to ensure a flush fit in 1/2 Inch drywall
- Angled side nails for rapid installation

### North American Specifications (UNSPSC)

UNSPSC	39121316 Ceiling box
IGCC	4448 Ceiling box
Brand Name	Carlon
Type	Ceiling Boxes
Special Features	Vapor-tight seal
Standard	UL e11461
Material	Polycarbonate
Color	Black
Cubic Capacity	26

### European Specifications (ETIM)

ETIM	EC002601 Box/housing for built-in mounting in the wall/ceiling
Mounting method	Other
Shape	Round
Construction type	Device connection box (round/square)
Equipped with	None
Length	101.6mm
Width	101.6mm
Depth	69.85-69.85mm
Mounting switching equipment	Screwing
With screws	N
Pipe locking	N
Pipe locking optional	N
Inlet from the rear	N
Material	Plastic
Colour	Black
Cover	None
Cover attachment	Not applicable
Sealable	N

### Packaging

Outer Quantity	50
Outer Dimensions (inches)	25.9x18.8x11.2
Weight Uom	36.5 lbs. per 100

### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 860 Ridge Lake Blvd.  
 Memphis, TN 38120  
 www.tnb.com

T&B Technical Support  
 MS 3B-50  
 860 Ridge Lake Blvd.  
 Memphis, TN 38120

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321

