

## MB-1

### One-Piece Mica Insulated Band Heater *(cont'd.)*

#### Specifications and Ordering Information *(continued)*

Watts	Volts	W/in <sup>2</sup>	Dimensions (In.)		Term.	Model	Stock	PCN	Wt. (Lbs.)
			Barrel Dia.	Heater Width					
600	240	26	2-3/4	3	I	MB2N3A1L2	NS	155395	0.5
400	240	31	2-3/4	1-1/2	P	MB2N1J1P1	NS	150800	0.6
200	120	25	3	1	A	MB3A1A1A1	NS	155408	1
200	240	25	3	1	A	MB3A1A1A2	NS	155416	1
200	240	25	3	1	T1	MB3A1A1P4	NS	155459	1
700	120	28	3	3	T1	MB3A3A1P1	NS	155694	1
400	240	28	3	1-1/2	P	MB3A1J1P1	NS	150279	0.7
700	240	28	3	3	T1	MB3A3A1P2	NS	155707	1
500	240	29	3	2	T1	MB3A2A1P1	NS	155651	1
300	240	32	3	1	P	MB3A1A1P1	NS	150261	0.7
500	240	35	3	1-1/2	P	MB3A1J1P2	NS	150826	0.7
400	240	42	3	1	P	MB3A1A1P2	NS	150818	0.7
500	240	43	3	1-1/2	L	MB3A1J1L3	NS	155619	1
400	240	27	3-1/8	1-1/2	P	MB3C1J1P1	NS	150834	0.7
300	240	31	3-1/8	1	P	MB3C1A1P1	NS	150287	0.7
400	240	27	3-1/4	1-1/2	P	MB3E1J1P1	NS	150842	0.7
400	240	28	3-1/4	1-1/2	T1	MB3E1J1P1	NS	155740	1
500	240	29	3-1/4	2	A	MB3E2A1A1	NS	155758	1
600	240	27	3-1/2	2	P	MB3J2A1P1	NS	150869	0.8
400	240	28	3-1/2	1-1/2	A	MB3J1J1A2	NS	155811	1
400	240	28	3-1/2	1-1/2	A	MB3J1J1L2	NS	155838	1
400	240	28	3-1/2	1-1/2	T1	MB3J1J1P2	NS	155846	1
500	120	30	3-1/2	1-1/2	T1	MB3J1J1P3	NS	155854	1
500	240	30	3-1/2	1-1/2	P	<b>MB3J1J1P1</b>	<b>S</b>	<b>150295</b>	0.7
300	240	30	3-1/2	1	L	MB3J1A1L2	NS	155790	1
600	240	30	3-1/2	2	T1	MB3J2A1P1	NS	155862	1
700	240	40	3-3/4	1-1/2	P	MB3N1J1P1	NS	150877	0.8
500	120	20	4	2-1/2	T1	MB4A2J1P1	NS	155918	1
550	240	25	4	2	T1	MB4A2A1P1	NS	155897	1
500	240	27	4	1-1/2	P	<b>MB4B1J1P1</b>	<b>S</b>	<b>150308</b>	0.8
800	240	35	4	2	T1	MB4A2A1P2	NS	155900	1
400	240	37	4	1	T1	MB4A1A1P1	NS	155870	1
1000	240	39	4	2-1/2	T1	MB4A2J1P3	NS	155934	1
650	240	40	4	1-1/2	T1	MB4A1J1P2	NS	155889	1
350	240	28	4-1/2	1	T1	MB4J1A1P1	NS	155969	1
1000	240	30	4-1/2	2-1/2	T1	MB4J2AJP1	NS	155993	1
650	240	31	4-1/2	1-1/2	P	MB4J1J1P1	NS	150316	0.8
800	240	28	5	2	T1	MB5A2A1P1	NS	156064	1
700	240	33	5	1-1/2	T1	MB5A1J1P1	NS	156048	1
1000	240	45	5	1-1/2	T1	MB5E1J1P2	NS	156080	1
600	240	24	5-1/4	1-1/2	P	MB5E1J1P1	NS	150949	0.9
900	240	35	5-1/2	1-1/2	P	MB5J1J1P1	NS	150965	0.9
300	240	20	6	1	A	MB6A1A1A2	NS	156136	1
600	240	23	6	1-1/2	T1	MB6A1J1P1	NS	156160	1
1500	240	28	6	3	T1	MB6A3A1P2	NS	156208	1
1450	240	34	6	2-1/2	T1	MB6A2J1P1	NS	156187	1
1,000	240	35	6-1/8	1-1/2	P	MB6C1J1P1	NS	150981	1
1000	120	27	6-1/2	2	T1	MB6J2A1P1	NS	156232	1
500	240	21	8	1	T1	MB8A1A1P1	NS	156371	1
1000	240	22	8	2	T1	MB8A2A1P1	NS	156419	1
950	240	27	8	1-1/2	T1	MB8A1J1P1	NS	156380	1
1200	240	34	8-1/2	1-1/2	T1	MB8J1J1P1	NS	156435	1
1300	240	33	9	1-1/2	T1	MB9A1J1P1	NS	156460	1

**Stock Status:** S = stock NS = non-stock

**To Order**—Specify model, PCN, volts, watts and quantity.

**Note** — Watt densities shown are based on heated area of contact surface only.