

Components

CB

Ceramic Band Heater (*cont'd.*)

Specifications and Ordering Information

Watts	W/In ²	Dimensions (In.)		Terminal Type	120V			240V		
		I.D.	Width		Model	Stock	PCN	Model	Stock	PCN
500	40	3	1-1/2	T2	CB3A1J1P1	NS	160012	CB3A1J1P2	NS	160020
700	26	3	3	T3	CB3A3A1P1	NS	160055	CB3A3A1P2	NS	160063
1500	40	3	4	T3	CB3A4A1P1	NS	160071	CB3A4A1P2	NS	160080
1350	28	3	6	T3	CB3A6A1P1	NS	160098	CB3A6A1P2	NS	160100
1800	35	3	6	T3	CB3A6A1P3	NS	160119	CB3A6A1P4	NS	160127
600	38	3-1/2	1-1/2	T2	—	—	—	CB3J1J1P1	NS	160135
650	30	3-1/2	2	T2	CB3J2A1P1	NS	160143	CB3J2A1P2	NS	160151
800	37	3-1/2	3	T3	CB3J3A1P1	NS	160160	CB3J3A1P2	NS	160178
1200	30	3-1/2	4	T3	—	—	—	CB3J4A1P1	NS	160186
1000	23	3-1/2	4-1/2	T3	CB3J4J1P1	NS	160194	CB3J4J1P2	NS	160207
800	22	4	2	T2	CB4A2A1P1	S	160223	CB4A2A1P2	S	160231
1200	35	4	3	T3	CB4A3A1P1	S	160240	CB4A3A1P2	NS	160258
1200	26	4	4	T3	—	—	—	CB4A4A1P1	NS	160266
2500	38	4	6	T3	—	—	—	CB4A6A1P1	S	160274
700	35	4-1/2	1-1/2	T2	CB4A6A1P3	S	160282	—	—	—
1100	40	4-1/2	2	T2	—	—	—	CB4J2A1P1	S	160290
1000	19	4-1/2	4	T3	CB4J4A1P1	S	160303	CB4J4A1P2	S	160311
2000	26	4-1/2	6	T3	—	—	—	CB4J6A1P1	S	160346
800	35	5	1-1/2	T2	—	—	—	CB5A1J1P1	S	160354
850	19	5	3	T3	CB5A3A1P1	S	160370	—	—	—
1250	28	5	3	T3	CB5A3A1P2	S	160389	CB5A3A1P3	S	160397
1600	35	5	3	T3	—	—	—	CB5A3A1P4	S	160400
1250	24	5	3-1/2	T3	CB5A3J1P1	S	160418	CB5A3J1P2	NS	160426
2200	38	5	4	T3	CB5A4A1P1	S	160434	CB5A4A1P2	S	160442
2750	32	5	6	T3	CB5A6A1P1	S	160450	CB5A6A1P2	S	160469
900	38	5-1/2	1-1/2	T2	CB5J1J1P1	S	160477	CB5J1J1P2	S	160485
1000	30	5-1/2	2	T2	CB5J2A1P1	S	160493	CB5J2A1P2	S	160506
1500	38	5-1/2	2-1/2	T2	—	—	—	CB5J2J1P1	S	160514
1200	25	5-1/2	3	T3	CB5J3A1P1	S	160522	CB5J3A1P2	S	160530
1550	25	5-1/2	4	T3	CB5J4A1P1	S	160549	CB5J4A1P2	S	160557
2000	24	5-1/2	5	T3	CB5J5A1P1	S	160565	CB5J5A1P2	S	160573
650	27	5-3/4	1-1/2	T2	—	—	—	CB5N1J1P1	S	160581
850	25	5-3/4	2	T2	CB5N2A1P1	S	160590	CB5N2A1P2	S	160602
1250	25	5-3/4	3	T3	CB5N3A1P1	S	160610	CB5N3A1P2	S	160629
1200	18	5-3/4	4	T3	CB5N4A1P1	S	160637	CB5N4A1P2	S	160645
1100	40	6	1-1/2	T2	—	—	—	CB6A1J1P1	S	160653
1000	28	6	2	T2	CB6A2A1P1	S	160661	CB6A2A1P2	S	160670
1500	35	6	2-1/2	T2	CB6A2J1P1	S	160709	CB6A2J1P2	S	160717
1600	29	6	3	T3	CB6A3A1P1	S	160725	CB6A3A1P2	S	160733
1450	21	6	4	T3	CB6A4A1P1	S	160741	CB6A4A1P2	S	160750
1800	20	6	5	T3	CB6A5A1P1	S	160768	CB6A5A1P2	S	160776
2000	22	6	5-1/2	T3	CB6A5J1P1	S	160784	CB6A5J1P2	S	160792
2000	19	6	6	T3	CB6A6A1P1	S	160805	CB6A6A1P2	S	160813
3000	28	6	6	T3	CB6A6A1P3	S	160821	CB6A6A1P4	S	160830

Note: For watt densities higher than 40 wpsi, consult factory.