

CIR 1/4 - 3/4" Dia. Cartridge Heater (cont'd.)

Specifications and Ordering Information

DIM (In.)		Watts	W/In ²	Model	120V		240V		Wt. (Lbs.)
Dia.	Sheath Length				Stock	PCN	Stock	PCN	
1/2" Diameter									
3/4	5	300	28	CIR-5052	S	244460	—	—	0.39
3/4	5	500	47	CIR-5051	—	—	S	281084	0.39
3/4	5	1,000	95	CIR-5050	NS	278070	NS	278088	0.39
3/4	6	350	27	CIR-5061	S	140281	S	275813	0.48
3/4	6	500	39	CIR-5065	S	244478	S	244486	0.48
3/4	6	750	58	CIR-5062	—	—	—	281092	0.48
3/4	6	1,000	78	CIR-5067	—	—	S	244494	0.48
3/4	6	1,100	85	CIR-5060	NS	278096	S	278109	0.48
3/4	6	1,500	117	CIR-5068	—	—	—	244507	0.48
3/4	6	2,000	155	CIR-5069	—	—	S	244515	0.48
3/4	7	500	33	CIR-5075	S	244523	—	244531	0.57
3/4	7	1,000	66	CIR-5072	—	—	S	244540	0.57
3/4	7-5/8	450	27	CIR-5077	S	140290	S	275821	0.61
3/4	7-5/8	1,300	78	CIR-5076	—	278117	S	278125	0.61
3/4	8	500	28	CIR-5085	NS	244558	NS	244566	0.64
3/4	8	1,000	57	CIR-5080	—	—	S	281105	0.64
3/4	8	1,500	85	CIR-5081	—	—	—	281113	0.64
3/4	8	2,000	113	CIR-5082	—	—	S	281121	0.64
3/4	9-1/8	500	25	CIR-5091	NS	140302	S	275830	0.73
3/4	10	1,000	45	CIR-5100	—	—	S	281130	0.79
3/4	10	2,000	90	CIR-5102	—	—	S	244574	0.79
3/4	10-1/2	550	23	CIR-5106	NS	140310	NS	275848	0.83
3/4	10-1/2	2,000	85	CIR-5105	S	278133	S	278141	0.83
3/4	11-7/8	600	22	CIR-5118	NS	140329	S	275856	0.91
3/4	12	1,000	37	CIR-5120	—	—	S	281148	0.92
3/4	12	2,000	74	CIR-5121	—	—	S	281156	0.92
3/4	12	3,000	111	CIR-5122	—	—	—	281164	0.92
3/4	12	4,000	148	CIR-5124	—	—	S	244582	0.92
3/4	13-3/8	650	21	CIR-5135	NS	140337	S	275864	1.02
3/4	13-3/8	2,500	83	CIR-5134	—	—	S	278150	1.02
3/4	14	1,250	40	CIR-5141	—	—	—	244590	1.07
3/4	14	2,500	80	CIR-5142	—	—	—	244603	1.07

Specifications and Ordering Information

DIM (In.)		Watts	W/in ²	Model	120V		240V		Wt. (Lbs.)
Dia.	Sheath Length				Stock	PCN	Stock	PCN	
3/4" Diameter									
3/4	14	4,500	142	CIR-5144	—	—	—	244611	1.07
3/4	14-7/8	750	22	CIR-5148	S	140345	S	275872	1.14
3/4	15	1,500	44	CIR-5150	—	—	—	281172	1.15
3/4	16	1,800	49	CIR-5162	—	—	—	244620	1.23
3/4	16	4,700	128	CIR-5165	—	—	—	244638	1.23
3/4	16-1/4	800	22	CIR-5163	—	—	S	140353	
3/4	17-3/4	850	21	CIR-5177	—	—	NS	275880	1.36
3/4	18	1,500	36	CIR-5180	—	—	—	281180	1.38
3/4	18	2,000	48	CIR-5182	—	—	—	244646	1.38
3/4	18	5,000	122	CIR-5185	—	—	—	244654	1.38
3/4	20	1,000	22	CIR-5204	—	—	NS	140361	
3/4	20	1,150	25	CIR-5202	—	—	—	244662	1.53
3/4	20	2,000	44	CIR-5201	—	—	—	281199	1.53
3/4	20	2,250	49	CIR-5203	—	—	—	244670	1.53
3/4	20	3,850	84	CIR-5200	—	—	S	278168	1.53
3/4	20	5,000	110	CIR-5205	—	—	—	244689	1.53
3/4	22	1,150	23	CIR-5220	—	—	S	140370	
3/4	24	1,250	23	CIR-5241	—	—	S	275899	1.84
3/4	24	1,375	25	CIR-5243	—	—	—	244697	1.84
3/4	24	2,500	42	CIR-5242	—	—	—	281201	1.84
3/4	24	2,750	50	CIR-5244	—	—	—	244700	1.84
3/4	24	4,600	83	CIR-5240	—	—	S	278176	1.84
3/4	24	5,000	85	CIR-5245	—	—	—	244718	1.84
3/4	30	2,500	37	CIR-5301	—	—	S	140388	
3/4	30	4,800	69	CIR-5300	—	—	S	278184	2.3
3/4	36	2,500	30	CIR-5362	—	—	—	244726	2.75
3/4	36	4,900	59	CIR-5360	—	—	NS	278192	2.75
3/4	48	5,000	45	CIR-5480	—	—	S	278205	3.7
Stock Status: S = stock NS = non-stock To Order —Specify model, PCN, watts, volts and quantity.									

Stock Status: S = stock NS = non-stock
To Order—Specify model, PCN, watts, volts and quantity.