

U-RAD-LT

Liquid-Tight, Double-Hairpin Element Radiant Heater (cont'd.)

Specifications and Ordering Information

kW	Volts	Length (In.)		Model	Stock	PCN	Optional Grille ²	Replacement Elements ¹	Wt. (Lbs.)
		Overall A	Heated B						
3.3	208	44-5/8	35-1/8	U-RAD-52VLT	NS	119490	(2) GR-2	(1) UTU-2VLT, (1) UTU-5VLT	18
3.3	240	44-5/8	35-1/8	U-RAD-52LT	NS	119482	(2) GR-2	(1) UTU-2LT, (1) UTU-5LT	18
3.3	275	44-5/8	35-1/8	U-RAD-52VLT	NS	119503	(2) GR-2	(1) UTU-2VLT, (1) UTU-5VLT	18
3.6	208	47-3/4	38-1/4	U-RAD-53VLT	NS	119520	(1) GR-4	(1) UTU-3VLT, (1) UTU-5VLT	19
3.6	240	47-3/4	38-1/4	U-RAD-53LT	NS	119511	(1) GR-4	(1) UTU-3LT, (1) UTU-5LT	19
3.6	275	47-3/4	38-1/4	U-RAD-53VLT	NS	119538	(1) GR-4	(1) UTU-3VLT, (1) UTU-5VLT	19
4.3	208	55-5/8	46-3/16	U-RAD-54VLT	NS	119562	(3) GR-2	(1) UTU-4VLT, (1) UTU-5VLT	21
4.3	240	55-5/8	46-3/16	U-RAD-54LT	NS	119546	(3) GR-2	(1) UTU-4LT, (1) UTU-5LT	21
4.3	275	55-5/8	46-3/16	U-RAD-54VLT	NS	119570	(3) GR-2	(1) UTU-4VLT, (1) UTU-5VLT	21
4.3	480	55-5/8	46-3/16	U-RAD-54LT	NS	119554	(3) GR-2	(1) UTU-4LT, (1) UTU-5LT	21
5	208	63-1/8	53-9/16	U-RAD-55VLT	NS	119600	(1) GR-5	(2) UTU-5VLT	22
5	240	63-1/8	53-9/16	U-RAD-55LT	NS	119589	(1) GR-5	(2) UTU-5LT	22
5	275	63-1/8	53-9/16	U-RAD-55VLT	NS	119597	(1) GR-5	(2) UTU-5VLT	22
5	480	63-1/8	53-9/16	U-RAD-55LT	NS	119618	(1) GR-5	(2) UTU-5LT	22
3.8	208	50-9/16	41-1/8	U-RAD-62VLT	NS	119634	(1) GR-2, (1) GR-3	(1) UTU-2VLT, (1) UTU-6VLT	20
3.8	240	50-9/16	41-1/8	U-RAD-62LT	NS	119626	(1) GR-2, (1) GR-3	(1) UTU-2LT, (1) UTU-6LT	20
3.8	275	50-9/16	41-1/8	U-RAD-62VLT	NS	119642	(1) GR-2, (1) GR-3	(1) UTU-2VLT, (1) UTU-6VLT	20
4.1	208	53-11/16	44-1/4	U-RAD-63VLT	NS	119669	(2) GR-3	(1) UTU-3VLT, (1) UTU-6VLT	21
4.1	240	53-11/16	44-1/4	U-RAD-63LT	NS	119650	(2) GR-3	(1) UTU-3LT, (1) UTU-6LT	21
4.1	275	53-11/16	44-1/4	U-RAD-63VLT	NS	119677	(2) GR-3	(1) UTU-3VLT, (1) UTU-6VLT	21
4.8	208	61-9/16	52-3/16	U-RAD-64VLT	NS	119706	(1) GR-5	(1) UTU-4VLT, (1) UTU-6VLT	23
4.8	240	61-9/16	52-3/16	U-RAD-64LT	NS	119685	(1) GR-5	(1) UTU-4LT, (1) UTU-6LT	23
4.8	275	61-9/16	52-3/16	U-RAD-64VLT	NS	119714	(1) GR-5	(1) UTU-4VLT, (1) UTU-6VLT	23
4.8	480	61-9/16	52-3/16	U-RAD-64LT	NS	119693	(1) GR-5	(1) UTU-4LT, (1) UTU-6LT	23
5.5	208	69-1/16	59-5/8	U-RAD-65VLT	NS	119749	(1) GR-3, (1) GR-4	(1) UTU-5VLT, (1) UTU-6VLT	24
5.5	240	69-1/16	59-5/8	U-RAD-65LT	NS	119722	(1) GR-3, (1) GR-4	(1) UTU-5LT, (1) UTU-6LT	24
5.5	275	69-1/16	59-5/8	U-RAD-65VLT	NS	119757	(1) GR-3, (1) GR-4	(1) UTU-5VLT, (1) UTU-6VLT	24
5.5	480	69-1/16	59-5/8	U-RAD-65LT	NS	119730	(1) GR-3, (1) GR-4	(1) UTU-5-LT, (1) UTU-6LT	24
6	208	75	65-5/8	U-RAD-66VLT	NS	119781	(1) GR-6	(2) UTU-6VLT	26
6	240	75	65-5/8	U-RAD-66LT	NS	119765	(1) GR-6	(2) UTU-6LT	26
6	275	75	65-5/8	U-RAD-66VLT	NS	119790	(1) GR-6	(2) UTU-6VLT	26
6	480	75	65-5/8	U-RAD-66LT	NS	119773	(1) GR-6	(2) UTU-6LT	26
4.4	208	56-11/16	47-1/4	U-RAD-72VLT	NS	119810	(1) GR-2, (1) GR-4	(1) UTU-2VLT, (1) UTU-7VLT	22
4.4	240	56-11/16	47-1/4	U-RAD-72LT	NS	119802	(1) GR-2, (1) GR-4	(1) UTU-2LT, (1) UTU-7LT	22
4.4	275	56-11/16	47-1/4	U-RAD-72VLT	NS	119829	(1) GR-2, (1) GR-4	(1) UTU-2VLT, (1) UTU-7VLT	22
4.7	208	59-13/16	50-3/8	U-RAD-73VLT	NS	119845	(3) GR-2	(1) UTU-3VLT, (1) UTU-7VLT	23
4.7	240	59-13/16	50-3/8	U-RAD-73LT	NS	119837	(3) GR-2	(1) UTU-3LT, (1) UTU-7LT	23
4.7	275	59-13/16	50-3/8	U-RAD-73VLT	NS	119853	(3) GR-2	(1) UTU-3VLT, (1) UTU-7VLT	23
5.4	208	67-11/16	58-1/4	U-RAD-74VLT	NS	119888	(1) GR-2, (1) GR-4	(1) UTU-4VLT, (1) UTU-7VLT	25
5.4	240	67-11/16	58-1/4	U-RAD-74LT	NS	119861	(1) GR-2, (1) GR-4	(1) UTU-4LT, (1) UTU-7LT	25
5.4	275	67-11/16	58-1/4	U-RAD-74VLT	NS	119896	(1) GR-2, (1) GR-4	(1) UTU-4VLT, (1) UTU-7VLT	25
5.4	480	67-11/16	58-1/4	U-RAD-74LT	NS	119870	(1) GR-2, (1) GR-4	(1) UTU-4LT, (1) UTU-7LT	25
6.1	208	75-3/16	65-5/8	U-RAD-75VLT	NS	119925	(1) GR-6	(1) UTU-5VLT, (1) UTU-7VLT	26
6.1	240	75-3/16	65-5/8	U-RAD-75LT	NS	119909	(1) GR-6	(1) UTU-5LT, (1) UTU-7LT	26
6.1	275	75-3/16	65-5/8	U-RAD-75VLT	NS	119933	(1) GR-6	(1) UTU-5VLT, (1) UTU-7VLT	26
6.1	480	75-3/16	65-5/8	U-RAD-75LT	NS	119917	(1) GR-6	(1) UTU-5LT, (1) UTU-7LT	26
6.6	208	81-1/8	71-3/4	U-RAD-76VLT	NS	119968	(1) GR-2, (1) GR-5	(1) UTU-6VLT, (1) UTU-7VLT	28
6.6	240	81-1/8	71-3/4	U-RAD-76LT	NS	119941	(1) GR-2, (1) GR-5	(1) UTU-6LT, (1) UTU-7LT	28
6.6	275	81-1/8	71-3/4	U-RAD-76VLT	NS	119976	(1) GR-2, (1) GR-5	(1) UTU-6VLT, (1) UTU-7VLT	28
6.6	480	81-1/8	71-3/4	U-RAD-76LT	NS	119950	(1) GR-2, (1) GR-5	(1) UTU-6LT, (1) UTU-7LT	28
7.2	208	87-1/4	77-7/8	U-RAD-77VLT	NS	120002	(2) GR-4	(2) UTU-7VLT	30
7.2	240	87-1/4	77-7/8	U-RAD-77LT	NS	119984	(2) GR-4	(2) UTU-7LT	30
7.2	275	87-1/4	77-7/8	U-RAD-77VLT	NS	120010	(2) GR-4	(2) UTU-7VLT	30
7.2	480	87-1/4	77-7/8	U-RAD-77LT	NS	119992	(2) GR-4	(2) UTU-7LT	30

METAL SHEATH
RADIANT

Stock Status: S = stock NS = non-stock

To Order—Specify model, PCN, kW, volts, quantity, optional grille and replacement elements (if needed).

1. Refer to Tubular Heaters section.

2. See Accessories in this section for ordering information.