

DU-RAD

Three Element Radiant Heater *(cont'd.)*

Specifications and Ordering Information

kW			Volts	Dimensions (In.)				Model	Stock	PCN	Optional Grille ²	Replacement Elements ¹		Wt. (Lbs.)
Total	Ea. End	Center		A	B	C	D					Center	End	
3.2	0.8	1.6	120	44-3/4	35-7/8	19-1/4	8-5/16	DU-RAD-240	NS	112205	(2) GR-2	UTU-40	UTU-2	10
3.2	0.8	1.6	240	44-3/4	35-7/8	19-1/4	8-5/16	DU-RAD-240	NS	112213	(2) GR-2	UTU-40	UTU-2	10
3.57	0.8	1.97	120	48-3/4	39-7/8	23-1/4	8-5/16	DU-RAD-248	NS	112221	(1) GR-4	UTU-48	UTU-2	11
3.57	0.8	1.97	240	48-3/4	39-7/8	23-1/4	8-5/16	DU-RAD-248	NS	112230	(1) GR-4	UTU-48	UTU-2	11
4.04	0.8	2.44	120	53-7/8	45	28-3/8	8-5/16	DU-RAD-258	NS	112248	(2) GR-3	UTU-58	UTU-2	11
4.04	0.8	2.44	240	53-7/8	45	28-3/8	8-5/16	DU-RAD-258	NS	112256	(2) GR-3	UTU-58	UTU-2	11
4.42	0.8	2.82	120	57-7/8	49	32-3/8	8-5/16	DU-RAD-266	NS	112264	(3) GR-2	UTU-66	UTU-2	12
4.42	0.8	2.82	240	57-7/8	49	32-3/8	8-5/16	DU-RAD-266	NS	112272	(3) GR-2	UTU-66	UTU-2	12
4.79	0.8	3.19	240	62	53-1/8	36-1/2	8-5/16	DU-RAD-274	NS	112299	(1) GR-5	UTU-74	UTU-2	13
5.17	0.8	3.57	240	66-1/16	57-3/16	40-9/16	8-5/16	DU-RAD-282	NS	112301	(1) GR-5	UTU-82	UTU-2	14
5.55	0.8	3.95	240	70-3/16	61-5/16	44-11/16	8-5/16	DU-RAD-290	NS	112310	(1) GR-3, (1) GR-4	UTU-90	UTU-2	15
6.12	0.8	4.52	240	76-9/16	67-5/16	50-11/16	8-5/16	DU-RAD-2102	NS	112328	(1) GR-6	UTU-102	UTU-2	16
6.59	0.8	4.99	240	81-5/16	72-7/16	55-13/16	8-5/16	DU-RAD-2112	NS	112336	(1) GR-6	UTU-112	UTU-2	16
7.16	0.8	5.56	240	87-1/2	78-5/8	62	8-5/16	DU-RAD-2124	NS	112344	(2) GR-4	UTU-124	UTU-2	32
7.73	0.8	6.13	240	93-1/2	84-5/8	68	8-5/16	DU-RAD-2136	NS	112352	(1) GR-2, (1) GR-6	UTU-136	UTU-2	36
8.3	0.8	6.7	240	99-5/8	90-3/4	74-1/8	8-5/16	DU-RAD-2148	NS	112360	(1) GR-3, (1) GR-6	UTU-148	UTU-2	37
8.7	0.8	7.1	240	103-11/16	94-13/16	78-3/16	8-5/16	DU-RAD-2156	NS	112379	(1) GR-4, (1) GR-5	UTU-156	UTU-2	40
9.05	0.8	7.45	240	107-13/16	98-15/16	82-5/16	8-5/16	DU-RAD-2164	NS	112387	(1) GR-3, (2) GR-4	UTU-164	UTU-2	41
9.43	0.8	7.83	240	112	103-1/8	86-1/2	8-5/16	DU-RAD-2172	NS	112395	(1) GR-3, (2) GR-4	UTU-127	UTU-2	43
3.8	1.1	1.6	120	51	42-1/8	19-1/4	11-7/16	DU-RAD-340	NS	112408	(1) GR-4	UTU-40	UTU-3	12
3.8	1.1	1.6	240	51	42-1/8	19-1/4	11-7/16	DU-RAD-340	NS	112416	(1) GR-4	UTU-40	UTU-3	12
4.17	1.1	1.97	120	55	46-1/8	23-1/4	11-7/16	DU-RAD-348	NS	112424	(2) GR-3	UTU-48	UTU-3	13
4.17	1.1	1.97	240	55	46-1/8	23-1/4	11-7/16	DU-RAD-348	NS	112432	(2) GR-3	UTU-48	UTU-3	13
4.64	1.1	2.44	120	60-1/8	51-1/8	28-3/8	11-7/16	DU-RAD-358	NS	112440	(3) GR-2	UTU-58	UTU-3	13
4.64	1.1	2.44	240	60-1/8	51-1/8	28-3/8	11-7/16	DU-RAD-358	NS	112459	(3) GR-2	UTU-58	UTU-3	13
5.02	1.1	2.82	120	64-1/8	55-1/4	32-3/8	11-7/16	DU-RAD-366	NS	112467	(1) GR-5	UTU-66	UTU-3	14
5.02	1.1	2.82	240	64-1/8	55-1/4	32-3/8	11-7/16	DU-RAD-366	NS	112475	(1) GR-5	UTU-66	UTU-3	14
5.39	1.1	3.19	120	68-1/4	59-3/8	36-1/2	11-7/16	DU-RAD-374	NS	112483	(1) GR-2, (1) GR-4	UTU-74	UTU-3	15
5.39	1.1	3.19	240	68-1/4	59-3/8	36-1/2	11-7/16	DU-RAD-374	NS	112491	(1) GR-2, (1) GR-4	UTU-74	UTU-3	15
5.77	1.1	3.57	240	72-5/16	63-7/16	40-9/16	11-7/16	DU-RAD-382	NS	112504	(1) GR-3, (1) GR-4	UTU-82	UTU-3	16
6.15	1.1	3.95	240	76-7/16	67-9/16	44-11/16	11-7/16	DU-RAD-390	NS	112512	(1) GR-6	UTU-90	UTU-3	17
6.72	1.1	4.52	240	82-7/16	73-9/16	50-11/16	11-7/16	DU-RAD-3102	NS	112520	(1) GR-2, (1) GR-5	UTU-102	UTU-3	19
7.19	1.1	4.99	240	87-9/16	78-11/16	55-13/16	11-7/16	DU-RAD-3112	NS	112539	(2) GR-4	UTU-112	UTU-3	32
7.76	1.1	5.56	240	93-3/4	84-7/8	62	11-7/16	DU-RAD-3124	NS	112547	(1) GR-2, (1) GR-6	UTU-124	UTU-3	36
8.33	1.1	6.13	240	99-3/4	90-7/8	68	11-7/16	DU-RAD-3136	NS	112555	(1) GR-3, (1) GR-6	UTU-136	UTU-3	37
8.9	1.1	6.7	240	105-7/8	97	74-1/8	11-7/16	DU-RAD-3148	NS	112563	(2) GR-2, (2) GR-4	UTU-148	UTU-3	40
9.3	1.1	7.1	240	109-15/16	101-3/16	78-3/16	11-7/16	DU-RAD-3156	NS	112571	(1) GR-3, (2) GR-4	UTU-156	UTU-3	42
9.65	1.1	7.45	240	114-1/16	105-3/16	82-5/16	11-7/16	DU-RAD-3164	NS	112580	(1) GR-4, (1) GR-6	UTU-164	UTU-3	43
10.03	1.1	7.83	240	118-1/4	109-3/8	86-1/2	11-7/16	DU-RAD-3172	NS	112598	(2) GR-5	UTU-172	UTU-3	47
5.2	1.8	1.6	240	66-3/4	57-7/8	19-1/4	19-3/8	DU-RAD-440	NS	112600	(1) GR-2, (1) GR-4	UTU-40	UTU-4	14
5.57	1.8	1.97	240	70-3/4	61-7/8	23-1/4	19-3/8	DU-RAD-448	NS	112619	(1) GR-3, (1) GR-4	UTU-48	UTU-4	15
6.04	1.8	2.44	240	75-7/8	67	28-3/8	19-3/8	DU-RAD-458	NS	112627	(1) GR-6	UTU-58	UTU-4	17
6.04	1.8	2.44	480	75-7/8	67	28-3/8	19-3/8	DU-RAD-458	NS	116310	(1) GR-6	UTU-58	UTU-4	17
6.42	1.8	2.82	240	79-7/8	71	32-3/8	19-3/8	DU-RAD-466	NS	112635	(3) GR-3	UTU-66	UTU-4	18
6.42	1.8	2.82	480	79-7/8	71	32-3/8	19-3/8	DU-RAD-466	NS	116345	(3) GR-3	UTU-66	UTU-4	18
6.79	1.8	3.19	240	84	75-1/3	36-1/2	19-3/8	DU-RAD-474	NS	112643	(1) GR-3, (1) GR-5	UTU-74	UTU-4	19
6.79	1.8	3.19	480	84	75-1/3	36-1/2	19-3/8	DU-RAD-474	NS	116370	(1) GR-3, (1) GR-5	UTU-74	UTU-4	19
7.17	1.8	3.57	240	88-1/16	79-3/16	40-9/16	19-3/8	DU-RAD-482	NS	112651	(2) GR-4	UTU-482	UTU-4	33
7.17	1.8	3.57	480	88-1/16	79-3/16	40-9/16	19-3/8	DU-RAD-482	NS	116409	(2) GR-4	UTU-482	UTU-4	33
7.55	1.8	3.95	240	92-3/16	83-5/16	44-11/16	19-3/8	DU-RAD-490	NS	112660	(1) GR-2, (1) GR-6	UTU-490	UTU-4	36
7.55	1.8	3.95	480	92-3/16	83-5/16	44-11/16	19-3/8	DU-RAD-490	NS	116433	(1) GR-2, (1) GR-6	UTU-490	UTU-4	36