

## DU-RAD

### Three Element Radiant Heater (cont'd.)

#### Specifications and Ordering Information

kW			Volts	Dimensions (In.)				Model	Stock	PCN	Optional Grille <sup>2</sup>	Replacement Elements <sup>1</sup>		Wt. (Lbs.)
Total	Ea. End	Center		A	B	C	D					Center	End	
8.12	1.8	4.52	240	98-3/16	89-5/16	50-11/16	19-3/8	DU-RAD-4102	NS	112678	(1) GR-3, (1) GR-6	UTU-102	UTU-4	37
8.12	1.8	4.52	480	98-3/16	89-5/16	50-11/16	19-3/8	DU-RAD-4102	NS	116468	(1) GR-3, (1) GR-6	UTU-102	UTU-4	37
8.59	1.8	4.99	240	103-5/16	94-7/16	55-13/16	19-3/8	DU-RAD-4112	NS	112686	(1) GR-4, (1) GR-5	UTU-112	UTU-4	40
8.59	1.8	4.99	480	103-5/16	94-7/16	55-13/16	19-3/8	DU-RAD-4112	NS	116492	(1) GR-4, (1) GR-5	UTU-112	UTU-4	40
9.16	1.8	5.56	240	109-1/2	100-5/8	62	19-3/8	DU-RAD-4124	NS	112694	(1) GR-3, (2) GR-4	UTU-124	UTU-4	42
9.16	1.8	5.56	480	109-1/2	100-5/8	62	19-3/8	DU-RAD-4124	NS	116521	(1) GR-3, (2) GR-4	UTU-124	UTU-4	42
9.73	1.8	6.13	240	115-1/2	106-5/8	68	19-3/8	DU-RAD-4136	NS	112707	(2) GR-5	UTU-136	UTU-4	45
9.73	1.8	6.13	480	115-1/2	106-5/8	68	19-3/8	DU-RAD-4136	NS	116556	(2) GR-5	UTU-136	UTU-4	45
10.3	1.8	6.7	240	121-5/8	112-3/4	74-1/8	19-3/8	DU-RAD-4148	NS	112715	(2) GR-5	UTU-148	UTU-4	47
10.3	1.8	6.7	480	121-5/8	112-3/4	74-1/8	19-3/8	DU-RAD-4148	NS	116580	(2) GR-5	UTU-148	UTU-4	47
10.7	1.8	7.1	240	125-11/16	116-13/16	78-3/16	19-3/8	DU-RAD-4156	NS	112723	(3) GR-4	UTU-156	UTU-4	49
10.7	1.8	7.1	480	125-11/16	116-13/16	78-3/16	19-3/8	DU-RAD-4156	NS	116610	(3) GR-4	UTU-156	UTU-4	49
11.05	1.8	7.45	240	129-13/16	120-15/16	82-5/16	19-3/8	DU-RAD-4164	NS	112731	(1) GR-5, (1) GR-6	UTU-164	UTU-4	50
11.05	1.8	7.45	480	129-13/16	120-15/16	82-5/16	19-3/8	DU-RAD-4164	NS	116644	(1) GR-5, (1) GR-6	UTU-164	UTU-4	50
11.43	1.8	7.83	240	134	125-1/8	86-1/2	19-3/8	DU-RAD-4172	NS	112740	(1) GR-2, (2) GR-5	UTU-172	UTU-4	52
11.43	1.8	7.83	480	134	125-1/8	86-1/2	19-3/8	DU-RAD-4172	NS	116679	(1) GR-2, (2) GR-5	UTU-172	UTU-4	52
6.6	2.5	1.6	240	81-5/8	72-3/4	19-1/4	26-13/16	DU-RAD-540	NS	112758	(1) GR-2, (1) GR-5	UTU-40	UTU-5	18
6.97	2.5	1.97	240	85-5/8	76-3/4	23-1/4	26-13/16	DU-RAD-548	NS	112766	(2) GR-4	UTU-48	UTU-5	19
7.44	2.5	2.44	240	90-3/4	81-7/8	28-3/8	26-13/16	DU-RAD-558	NS	112774	(1) GR-2, (1) GR-6	UTU-58	UTU-5	33
7.44	2.5	2.44	480	90-3/4	81-7/8	28-3/8	26-13/16	DU-RAD-558	NS	112782	(1) GR-2, (1) GR-6	UTU-58	UTU-5	33
7.82	2.5	2.82	240	94-3/4	85-7/8	32-3/8	26-13/16	DU-RAD-566	NS	112790	(1) GR-2, (1) GR-6	UTU-66	UTU-5	36
7.82	2.5	2.82	480	94-3/4	85-7/8	32-3/8	26-13/16	DU-RAD-566	NS	112803	(1) GR-2, (1) GR-6	UTU-66	UTU-5	36
8.19	2.5	3.19	240	98-7/8	90	36-1/2	26-13/16	DU-RAD-574	NS	112811	(1) GR-3, (1) GR-6	UTU-74	UTU-5	37
8.19	2.5	3.19	480	98-7/8	90	36-1/2	26-13/16	DU-RAD-574	NS	112820	(1) GR-3, (1) GR-6	UTU-74	UTU-5	37
8.57	2.5	3.57	240	102-15/16	94-1/16	40-9/16	26-13/16	DU-RAD-582	NS	112838	(1) GR-2, (2) GR-4	UTU-82	UTU-5	40
8.57	2.5	3.57	480	102-15/16	94-1/16	40-9/16	26-13/16	DU-RAD-582	NS	112846	(1) GR-2, (2) GR-4	UTU-82	UTU-5	40
8.95	2.5	3.95	240	107-1/16	98-3/16	44-11/16	26-13/16	DU-RAD-590	NS	112854	(1) GR-3, (1) GR-4	UTU-90	UTU-5	42
8.95	2.5	3.95	480	107-1/16	98-3/16	44-11/16	26-13/16	DU-RAD-590	NS	112862	(1) GR-3, (2) GR-4	UTU-90	UTU-5	42
9.52	2.5	4.52	240	113-1/16	104-3/16	50-11/16	26-13/16	DU-RAD-5102	NS	112870	(1) GR-4, (1) GR-6	UTU-102	UTU-5	45
9.52	2.5	4.52	480	113-1/16	104-3/16	50-11/16	26-13/16	DU-RAD-5102	NS	112889	(1) GR-4, (1) GR-6	UTU-102	UTU-5	45
9.99	2.5	4.99	240	118-3/16	109-5/16	55-13/16	26-13/16	DU-RAD-5112	NS	112897	(2) GR-5	UTU-112	UTU-5	47
9.99	2.5	4.99	480	118-3/16	109-5/16	55-13/16	26-13/16	DU-RAD-5112	NS	112900	(2) GR-5	UTU-112	UTU-5	47
10.56	2.5	5.56	240	124-3/8	115-1/2	62	26-13/16	DU-RAD-5124	NS	112918	(3) GR-4	UTU-124	UTU-5	49
10.56	2.5	5.56	480	124-3/8	115-1/2	62	26-13/16	DU-RAD-5124	NS	112926	(3) GR-4	UTU-124	UTU-5	49
11.13	2.5	6.13	240	130-3/8	121-1/2	68	26-13/16	DU-RAD-5136	NS	112934	(1) GR-5, (1) GR-6	UTU-136	UTU-5	50
11.13	2.5	6.13	480	130-3/8	121-1/2	68	26-13/16	DU-RAD-5136	NS	112942	(1) GR-5, (1) GR-6	UTU-136	UTU-5	50
11.7	2.5	6.7	240	136-1/2	127-5/8	74-1/8	26-13/16	DU-RAD-5148	NS	112950	(1) GR-2, (1) GR-5	UTU-148	UTU-5	52
11.7	2.5	6.7	480	136-1/2	127-5/8	74-1/8	26-13/16	DU-RAD-5148	NS	112969	(1) GR-2, (1) GR-5	UTU-148	UTU-5	52
12.1	2.5	7.1	240	140-9/16	131-11/16	78-3/16	26-13/16	DU-RAD-5156	NS	112977	(2) GR-6	UTU-156	UTU-5	53
12.1	2.5	7.1	480	140-9/16	131-11/16	78-3/16	26-13/16	DU-RAD-5156	NS	112985	(2) GR-6	UTU-156	UTU-5	53
12.45	2.5	7.45	240	144-11/16	135-13/16	82-5/16	26-13/16	DU-RAD-5164	NS	112993	(2) GR-6	UTU-164	UTU-5	54
12.45	2.5	7.45	480	144-11/16	135-13/16	82-5/16	26-13/16	DU-RAD-5164	NS	113005	(2) GR-6	UTU-164	UTU-5	54
12.83	2.5	7.83	240	148-7/8	140	86-1/2	26-13/16	DU-RAD-5172	NS	113013	(2) GR-6	UTU-172	UTU-5	55
12.83	2.5	7.83	480	148-7/8	140	86-1/2	26-13/16	DU-RAD-5172	NS	113021	(2) GR-6	UTU-172	UTU-5	55
7.6	3	1.6	240	93-3/4	84-7/8	19-1/4	32-13/16	DU-RAD-640	NS	113030	(1) GR-2, (1) GR-6	UTU-40	UTU-6	36
7.97	3	1.97	240	97-3/4	88-7/8	23-1/4	32-13/16	DU-RAD-648	NS	113048	(1) GR-3, (1) GR-6	UTU-48	UTU-6	37
8.44	3	2.44	240	102-7/8	94	28-3/8	32-13/16	DU-RAD-658	NS	113056	(1) GR-2, (1) GR-4	UTU-58	UTU-6	40
8.44	3	2.44	480	102-7/8	94	28-3/8	32-13/16	DU-RAD-658	NS	113064	(1) GR-2, (1) GR-4	UTU-58	UTU-6	40
8.82	3	2.82	240	106-7/8	98	32-3/8	32-13/16	DU-RAD-666	NS	113072	(1) GR-2, (1) GR-4	UTU-66	UTU-6	41
8.82	3	2.82	480	106-7/8	98	32-3/8	32-13/16	DU-RAD-666	NS	113080	(1) GR-2, (1) GR-4	UTU-66	UTU-6	41
9.19	3	3.19	240	111	102-1/8	36-1/2	32-13/16	DU-RAD-674	NS	113099	(1) GR-3, (1) GR-4	UTU-74	UTU-6	43
9.19	3	3.19	480	111	102-1/8	36-1/2	32-13/16	DU-RAD-674	NS	113101	(1) GR-3, (1) GR-4	UTU-74	UTU-6	43

METAL SHEATH  
RADIANT