

UB High Capacity Horizontal Blower Heater

| Electrical (60 Hz) | | | | Motor | | | | Air Delivery | | | | | Ordering | | | |
|--------------------|-------|-------|------|-------|-------|-----|-------|--------------|-------|-----------------|--------------------|-------------------|----------------|----------|---------------|------------|
| kW | Volts | Phase | Amps | Volts | Phase | HP | RPM | CFM | FPM | Temp. Rise (°F) | Horiz. Throw (Ft.) | Mtg. Height (Ft.) | Model | Stock | PCN | Wt. (Lbs.) |
| 35 | 600 | 3 | 33.7 | 115 | 1 | 1/3 | 1,550 | 2,500 | 1,040 | 47 | 54 | 14 | UB-3502 | NS | 333286 | 210 |
| 35 | 600 | 3 | 33.7 | 230 | 1 | 1/3 | 1,550 | 2,500 | 1,040 | 47 | 54 | 14 | UB-3502 | NS | 333294 | 210 |
| 35 | 600 | 3 | 33.7 | 230 | 1 | 1/3 | 1,550 | 2,500 | 1,040 | 47 | 54 | 14 | UB-3502 | NS | 333307 | 210 |
| 40 | 480 | 1 | 83.3 | 115 | 1 | 1/3 | 1,550 | 2,500 | 1,040 | 53 | 54 | 15 | UB-4002 | NS | 333315 | 210 |
| 40 | 480 | 1 | 83.3 | 115 | 1 | 1/3 | 1,550 | 2,500 | 1,040 | 53 | 54 | 15 | UB-4002 | NS | 333323 | 210 |
| 40 | 480 | 1 | 83.3 | 230 | 1 | 1/3 | 1,550 | 2,500 | 1,040 | 53 | 54 | 15 | UB-4002 | NS | 333331 | 210 |
| 40 | 480 | 1 | 83.3 | 230 | 1 | 1/3 | 1,550 | 2,500 | 1,040 | 53 | 54 | 15 | UB-4002 | NS | 333340 | 210 |
| 40 | 480 | 3 | 48.2 | 115 | 1 | 1/3 | 1,550 | 2,500 | 1,040 | 53 | 54 | 15 | UB-4002 | NS | 333358 | 210 |
| 40 | 480 | 3 | 48.2 | 115 | 1 | 1/3 | 1,550 | 2,500 | 1,040 | 53 | 54 | 15 | UB-4002 | NS | 333366 | 210 |
| 40 | 480 | 3 | 48.2 | 230 | 1 | 1/3 | 1,550 | 2,500 | 1,040 | 53 | 54 | 15 | UB-4002 | NS | 333374 | 210 |
| 40 | 480 | 3 | 48.2 | 230 | 1 | 1/3 | 1,500 | 2,500 | 1,040 | 53 | 54 | 15 | UB-4002 | NS | 333382 | 210 |
| 40 | 480 | 3 | 48.2 | 460 | 3 | 1/3 | 1,725 | 2,800 | 1,165 | 48 | 54 | 15 | UB-4002 | NS | 333390 | 210 |
| 40 | 480 | 3 | 48.2 | 460 | 3 | 1/3 | 1,725 | 2,800 | 1,165 | 48 | 54 | 15 | UB-4002 | NS | 333403 | 210 |
| 40 | 550 | 3 | 42 | 115 | 1 | 1/3 | 1,550 | 2,500 | 1,040 | 53 | 54 | 15 | UB-4002 | NS | 333411 | 210 |
| 40 | 550 | 3 | 42 | 115 | 1 | 1/3 | 1,550 | 2,500 | 1,040 | 53 | 54 | 15 | UB-4002 | NS | 333420 | 210 |
| 40 | 550 | 3 | 42 | 230 | 1 | 1/3 | 1,550 | 2,500 | 1,040 | 53 | 54 | 15 | UB-4002 | NS | 333438 | 210 |
| 40 | 550 | 3 | 42 | 230 | 1 | 1/3 | 1,550 | 2,500 | 1,040 | 53 | 54 | 15 | UB-4002 | NS | 333446 | 210 |
| 40 | 575 | 3 | 40.2 | 115 | 1 | 1/3 | 1,550 | 2,500 | 1,040 | 53 | 54 | 15 | UB-4002 | NS | 333454 | 210 |
| 40 | 575 | 3 | 40.2 | 115 | 1 | 1/3 | 1,550 | 2,500 | 1,040 | 53 | 54 | 15 | UB-4002 | NS | 333462 | 210 |
| 40 | 575 | 3 | 40.2 | 230 | 1 | 1/3 | 1,550 | 2,500 | 1,040 | 53 | 54 | 15 | UB-4002 | NS | 333470 | 210 |
| 40 | 575 | 3 | 40.2 | 230 | 1 | 1/3 | 1,550 | 2,500 | 1,040 | 53 | 54 | 15 | UB-4002 | NS | 333489 | 210 |
| 40 | 600 | 3 | 38.5 | 115 | 1 | 1/3 | 1,550 | 2,500 | 1,040 | 53 | 54 | 15 | UB-4002 | NS | 333497 | 210 |
| 40 | 600 | 3 | 38.5 | 115 | 1 | 1/3 | 1,550 | 2,500 | 1,040 | 53 | 54 | 15 | UB-4002 | NS | 333500 | 210 |
| 40 | 600 | 3 | 38.5 | 230 | 1 | 1/3 | 1,550 | 2,500 | 1,040 | 53 | 54 | 15 | UB-4002 | NS | 333518 | 210 |
| 40 | 600 | 3 | 38.5 | 230 | 1 | 1/3 | 1,550 | 2,500 | 1,040 | 53 | 54 | 15 | UB-4002 | NS | 333526 | 210 |
| 45 | 480 | 1 | 93.8 | 230 | 1 | 1/3 | 1,550 | 2,500 | 1,040 | 60 | 54 | 17 | UB-4502 | NS | 333534 | 210 |
| 45 | 480 | 1 | 93.8 | 230 | 1 | 1/3 | 1,550 | 2,500 | 1,040 | 60 | 54 | 17 | UB-4502 | NS | 333542 | 210 |
| 45 | 480 | 3 | 54.2 | 115 | 1 | 1/3 | 1,550 | 2,500 | 1,040 | 60 | 54 | 17 | UB-4502 | NS | 333550 | 210 |
| 45 | 480 | 3 | 54.2 | 115 | 1 | 1/3 | 1,550 | 2,500 | 1,040 | 60 | 54 | 17 | UB-4502 | NS | 333569 | 210 |
| 45 | 480 | 3 | 54.2 | 230 | 1 | 1/3 | 1,550 | 2,500 | 1,040 | 60 | 54 | 17 | UB-4502 | NS | 333577 | 210 |
| 45 | 480 | 3 | 54.2 | 230 | 1 | 1/3 | 1,550 | 2,500 | 1,040 | 60 | 54 | 17 | UB-4502 | NS | 333585 | 210 |
| 45 | 480 | 3 | 54.2 | 460 | 3 | 1/3 | 1,725 | 2,800 | 1,165 | 54 | 54 | 17 | UB-4502 | NS | 333593 | 210 |
| 45 | 480 | 3 | 54.2 | 460 | 3 | 1/3 | 1,725 | 2,800 | 1,165 | 54 | 54 | 17 | UB-4502 | NS | 333606 | 210 |
| 45 | 550 | 3 | 47.3 | 115 | 1 | 1/3 | 1,550 | 2,500 | 1,040 | 60 | 54 | 17 | UB-4502 | NS | 333614 | 210 |
| 45 | 550 | 3 | 47.3 | 115 | 1 | 1/3 | 1,550 | 2,500 | 1,040 | 60 | 54 | 17 | UB-4502 | NS | 333622 | 210 |
| 45 | 550 | 3 | 47.3 | 230 | 1 | 1/3 | 1,550 | 2,500 | 1,040 | 60 | 54 | 17 | UB-4502 | NS | 333630 | 210 |
| 45 | 550 | 3 | 47.3 | 230 | 1 | 1/3 | 1,550 | 2,500 | 1,040 | 60 | 54 | 17 | UB-4502 | NS | 333649 | 210 |
| 45 | 575 | 3 | 45.2 | 115 | 1 | 1/3 | 1,550 | 2,500 | 1,040 | 60 | 54 | 17 | UB-4502 | NS | 333657 | 210 |
| 45 | 575 | 3 | 45.2 | 115 | 1 | 1/3 | 1,550 | 2,500 | 1,040 | 60 | 54 | 17 | UB-4502 | NS | 333665 | 210 |
| 45 | 575 | 3 | 45.2 | 230 | 1 | 1/3 | 1,550 | 2,500 | 1,040 | 60 | 54 | 17 | UB-4502 | NS | 333673 | 210 |
| 45 | 575 | 3 | 45.2 | 230 | 1 | 1/3 | 1,550 | 2,500 | 1,040 | 60 | 54 | 17 | UB-4502 | NS | 333681 | 210 |
| 45 | 600 | 3 | 43.4 | 115 | 1 | 1/3 | 1,550 | 2,500 | 1,040 | 60 | 54 | 17 | UB-4502 | NS | 333690 | 210 |
| 45 | 600 | 3 | 43.4 | 115 | 1 | 1/3 | 1,550 | 2,500 | 1,040 | 60 | 54 | 17 | UB-4502 | NS | 333702 | 210 |
| 45 | 600 | 3 | 43.4 | 230 | 1 | 1/3 | 1,550 | 2,500 | 1,040 | 60 | 54 | 17 | UB-4502 | NS | 333710 | 210 |
| 45 | 600 | 3 | 43.4 | 230 | 1 | 1/3 | 1,550 | 2,500 | 1,040 | 60 | 54 | 17 | UB-4502 | NS | 333729 | 210 |
| 50 | 480 | 3 | 60.2 | 115 | 1 | 1/3 | 1,550 | 2,500 | 1,040 | 67 | 54 | 17 | UB-5002 | NS | 333737 | 210 |
| 50 | 480 | 3 | 60.2 | 115 | 1 | 1/3 | 1,550 | 2,500 | 1,040 | 67 | 54 | 17 | UB-5002 | NS | 333745 | 210 |
| 50 | 480 | 3 | 60.2 | 230 | 1 | 1/3 | 1,550 | 2,500 | 1,040 | 67 | 54 | 17 | UB-5002 | NS | 333753 | 210 |
| 50 | 480 | 3 | 60.2 | 230 | 1 | 1/3 | 1,550 | 2,500 | 1,040 | 67 | 54 | 17 | UB-5002 | NS | 333761 | 210 |
| 50 | 480 | 3 | 60.2 | 460 | 3 | 1/3 | 1,725 | 2,800 | 1,165 | 60 | 54 | 17 | UB-5002 | NS | 333770 | 210 |
| 50 | 480 | 3 | 60.2 | 460 | 3 | 1/3 | 1,725 | 2,800 | 1,165 | 60 | 54 | 17 | UB-5002 | S | 333788 | 210 |
| 50 | 550 | 3 | 52.5 | 115 | 1 | 1/3 | 1,550 | 2,500 | 1,040 | 67 | 54 | 17 | UB-5002 | NS | 333796 | 210 |
| 50 | 550 | 3 | 52.5 | 115 | 1 | 1/3 | 1,550 | 2,500 | 1,040 | 67 | 54 | 17 | UB-5002 | NS | 333809 | 210 |
| 50 | 550 | 3 | 52.5 | 230 | 1 | 1/3 | 1,550 | 2,500 | 1,040 | 67 | 54 | 17 | UB-5002 | NS | 333817 | 210 |
| 50 | 550 | 3 | 52.5 | 230 | 1 | 1/3 | 1,550 | 2,500 | 1,040 | 67 | 54 | 17 | UB-5002 | NS | 333825 | 210 |
| 50 | 575 | 3 | 50.3 | 115 | 1 | 1/3 | 1,550 | 2,500 | 1,040 | 67 | 54 | 17 | UB-5002 | NS | 333833 | 210 |
| 50 | 575 | 3 | 50.3 | 115 | 1 | 1/3 | 1,550 | 2,500 | 1,040 | 67 | 54 | 17 | UB-5002 | NS | 333841 | 210 |
| 50 | 575 | 3 | 50.3 | 230 | 1 | 1/3 | 1,550 | 2,500 | 1,040 | 67 | 54 | 17 | UB-5002 | NS | 333850 | 210 |
| 50 | 575 | 3 | 50.3 | 230 | 1 | 1/3 | 1,550 | 2,500 | 1,040 | 67 | 54 | 17 | UB-5002 | NS | 333868 | 210 |
| 50 | 600 | 3 | 48.2 | 115 | 1 | 1/3 | 1,550 | 2,500 | 1,040 | 67 | 54 | 17 | UB-5002 | NS | 333876 | 210 |
| 50 | 600 | 3 | 48.2 | 115 | 1 | 1/3 | 1,550 | 2,500 | 1,040 | 67 | 54 | 17 | UB-5002 | NS | 333884 | 210 |
| 50 | 600 | 3 | 48.2 | 230 | 1 | 1/3 | 1,550 | 2,500 | 1,040 | 67 | 54 | 17 | UB-5002 | NS | 333892 | 210 |
| 50 | 600 | 3 | 48.2 | 230 | 1 | 1/3 | 1,550 | 2,500 | 1,040 | 67 | 54 | 17 | UB-5002 | NS | 333905 | 210 |

Stock Status: S = stock NS = non-stock
To Order—Specify model, PCN, kW, volts, phase and quantity.

1. Not UL Listed.

Other Note — Up to 600V available, contact your Local Chromalox Sales office.

INDUSTRIAL