

DRA Portable Spot Industrial Salamander Blower Heater (cont'd.)

Specifications and Ordering Information

kW	Volts	Phase	Amps ¹	BTU/H	HP	CFM	Temp. Rise °F ²	Model	Stock	PCN	Wt. (Lbs.)
7.5	208	1 and 3	36.3/21.0	25,590	0.06	1070	23	DRA-07-83	NS	295523	65
7.5/5.6	240/208	1 and 3	31.5/18.3 ³	25,590	0.06	1070	23	DRA-07-23	S	295531	65
9.75	208	1 and 3	47.1/27.3	33,267	0.06	1070	31	DRA-10-83	S	295540	65
10/7.5	240/208	1 and 3	40.8/23.7 ³	33,267	0.06	1070	31	DRA-10-23	S	295558	65
15	208	3	41.8	51,180	0.06	1070	46	DRA-15-83	NS	295566	65
15/11.2	240/208	3	36.3 ³	51,180	0.06	1070	46	DRA-15-23	S	295574	65
15	480	1 and 3	31.4	51,180	0.06	1070	46	DRA-15-43	S	295582	65
15	600	1 and 3	25.2	51,180	0.06	1070	46	DRA-15-93	NS	295596	65
19.5/15	240/208	3	47.1 ³	66,534	0.06	1070	61	DRA-20-23	NS	295603	75
20	480	1 and 3	42.0	68,240	0.06	1070	62	DRA-20-43	S	295611	75
20	600	1 and 3	33.5	68,240	0.06	1070	62	DRA-20-93	NS	295620	75
30	480	3	36.3	102,360	0.06	1070	92	DRA-30-43	S	295638	75
30	600	3	29.1	102,360	0.06	1070	92	DRA-30-93	NS	295646	75

Stock Status: S = stock NS = non-stock
To Order—Specify model, PCN, kW, volts, phase and quantity.

1. Includes motor amps
2. Temperature rise at 240V operation
3. 208V amperage is 86% of 240V value

Models designated 1 and 3 can be field converted from three phase to single phase. Consult product installation, operation, and maintenance manual for details.

All models factory pre-wired with an 8 foot cord and plug for use in 3 phase operation (See table 1 factory installed plug and cord information)

Factory Installed Plug and Cord Data

Model	Plug Type	Cable Type	Model	Plug Type	Cable Type
DRA-07-83	NEMA 18-30P, Straight Blade	10 AWG, 4 Wire	DRA-15-93	NEMA 17-30P, Twist-Lock	12 AWG, 4 Wire
DRA-07-23	NEMA 18-30P, Straight Blade	10 AWG, 4 Wire	DRA-20-23	NEMA 15-50P, Straight Blade	4 AWG, 4 Wire
DRA-10-83	NEMA 18-30P, Straight Blade	8 AWG, 4 Wire	DRA-20-43	NEMA 16-30P, Twist-Lock	8 AWG, 4 Wire
DRA-10-23	NEMA 18-30P, Straight Blade	8 AWG, 4 Wire	DRA-20-93	NEMA 17-30P, Twist-Lock	10 AWG, 4 Wire
DRA-15-83	NEMA 18-50P, Straight Blade	6 AWG, 4 Wire	DRA-30-43	Non-NEMA 50A, Twist-Lock	6 AWG, 4 Wire
DRA-15-23	NEMA 15-50P, Straight Blade	6 AWG, 4 Wire	DRA-30-93	Non-NEMA 50A, Twist-Lock	8 AWG, 4 Wire
DRA-15-43	NEMA 16-30P, Twist-Lock	10 AWG, 4 Wire			

Standard Locking Plugs

Plug Type	Catalog Number	Description	Volts	Amps	NEMA#	Fits Cable Dia. (In.)	Stock	PCN	Wt. (Lbs.)
LOCKING	PGL-15-20	3 Pole, 4 Wire	250	20	L15-20	.385 to .780	NS	338845 / 511556014	0.5
LOCKING	PGL-16-30	3 Pole, 4 Wire	480	30	L16-30	.595 to 1.150	NS	338861 / 511556023	0.5
LOCKING	PGL-17-30	3 Pole, 4 Wire	600	30	L17-30	.595 to 1.150	S	338870 / 511556032	0.5
LOCKING	PGL-3763C	2 Pole, 3 Wire	600	50	N/A	.750 to 1.125	NS	338917 / 511556033	0.5
LOCKING	PGL-3765C	3 Pole, 4 Wire	600	50	N/A	.750 to 1.125	NS	338925 / 511556034	0.5
NON LOCKING	PGN-6-50	2 Pole, 3 Wire	250	50	6-50	.625 to 1.187	S	338888 / 511506014	0.5
NON LOCKING	PGN-15-20	3 Pole, 4 Wire	250	20	15-20	.390 to .775	S	338896 / 511506006	0.5
NON LOCKING	PGN-18-30	4 Pole, 4 Wire	208	30	18-30	.625 to 1.310	NS	511506026	0.5
NON LOCKING	PGN-18-50	4 Pole, 4 Wire	208	30	18-50	.625 to 1.310	NS	511506024	0.5
LOCKING	PGL-8165C	3 Pole, 4 Wire	480	50	N/A	.92 to 1.2	NS	511556031	0.5
NON LOCKING	PGN-8461C	3 Pole, 4 Wire	250	60	N/A	.625 to 1.310	NS	511506028	0.5

Stock Status: S = stock NS = non-stock
To Order—Specify model, PCN, kW, volts, phase and quantity.

FASTShip

Same-day shipping on stock item orders received before 4 pm CST.
3-day shipping on assembly-stock items.