

## CXH-A

### Explosion Proof Blower Heater for Hazardous Locations *(cont'd.)*

Electrical (60 Hz)				Motor				Air Delivery				Ordering				
kW	Volts	Phase	Full Load Amps	Control Volts	Phase	HP	RPM	Air Flow ft <sup>3</sup> /min (m <sup>3</sup> /hr)	Air Speed ft/min (m/min)	Temp. Rise °F (°C)	Horiz. Throw Ft. (mm)	Mtg. Height Ft. (mm.)	Model	Stock	PCN	Wt. (Lbs.)
10	240	1	44	120	1	1/4	1,725	840 (1427)	1070 (326.1)	36 (20.0)	32 (9.8)	10 (3.0)	CXH-A-10-21-32-00-20EP	NS	026374	140 (63.6)
10	240	3	25.5	120	3	1/4	1,725	840 (1427)	1070 (326.1)	36 (20.0)	32 (9.8)	10 (3.0)	CXH-A-10-23-32-00-20EP	NS	026382	140 (63.6)
10	480	3	12.7	120	3	1/4	1,725	840 (1427)	1070 (326.1)	36 (20.0)	32 (9.8)	10 (3.0)	<b>CXH-A-10-43-32-00-20EP</b>	<b>S</b>	<b>025101</b>	140 (63.6)
10	575	3	10.6	120	3	1/4	1,725	840 (1427)	1070 (326.1)	36 (20.0)	32 (9.8)	10 (3.0)	CXH-A-10-63-32-00-20EP	NS	026390	140 (63.6)
10	208	3	29.2	24	3	1/4	1,725	840 (1427)	1070 (326.1)	36 (20.0)	32 (9.8)	10 (3.0)	CXH-A-10-83-30-00-20EP	NS	026403	140 (63.6)
10	240	1	44	24	1	1/4	1,725	840 (1427)	1070 (326.1)	36 (20.0)	32 (9.8)	10 (3.0)	CXH-A-10-21-30-00-20EP	NS	026411	140 (63.6)
10	240	3	25.5	24	3	1/4	1,725	840 (1427)	1070 (326.1)	36 (20.0)	32 (9.8)	10 (3.0)	CXH-A-10-23-30-00-20EP	NS	026420	140 (63.6)
10	480	3	12.7	24	3	1/4	1,725	840 (1427)	1070 (326.1)	36 (20.0)	32 (9.8)	10 (3.0)	CXH-A-10-43-30-00-20EP	NS	026438	140 (63.6)
10	575	3	10.6	24	3	1/4	1,725	840 (1427)	1070 (326.1)	36 (20.0)	32 (9.8)	10 (3.0)	CXH-A-10-63-30-00-20EP	NS	026446	140 (63.6)
15	208	3	43	120	3	1/4	1,725	1450 (2464)	1040 (317.0)	31 (17.2)	47 (14.3)	10 (3.0)	CXH-A-15-83-32-00-20EP	NS	026454	160 (72.7)
15	240	3	37.5	120	3	1/4	1,725	1450 (2464)	1040 (317.0)	31 (17.2)	47 (14.3)	10 (3.0)	CXH-A-15-23-32-00-20EP	NS	026462	160 (72.7)
15	480	3	18.7	120	3	1/4	1,725	1450 (2464)	1040 (317.0)	31 (17.2)	47 (14.3)	10 (3.0)	<b>CXH-A-15-43-32-00-20EP</b>	<b>S</b>	<b>026470</b>	160 (72.7)
15	575	3	15.7	120	3	1/4	1,725	1450 (2464)	1040 (317.0)	31 (17.2)	47 (14.3)	10 (3.0)	CXH-A-15-63-32-00-20EP	NS	026489	160 (72.7)
15	208	3	43	24	3	1/4	1,725	1450 (2464)	1040 (317.0)	31 (17.2)	47 (14.3)	10 (3.0)	CXH-A-15-83-30-00-20EP	NS	026497	160 (72.7)
15	240	3	37.5	24	3	1/4	1,725	1450 (2464)	1040 (317.0)	31 (17.2)	47 (14.3)	10 (3.0)	CXH-A-15-23-30-00-20EP	NS	026500	160 (72.7)
15	480	3	18.7	24	3	1/4	1,725	1450 (2464)	1040 (317.0)	31 (17.2)	47 (14.3)	10 (3.0)	CXH-A-15-43-30-00-20EP	NS	026518	160 (72.7)
15	575	3	15.7	24	3	1/4	1,725	1450 (2464)	1040 (317.0)	31 (17.2)	47 (14.3)	10 (3.0)	CXH-A-15-63-30-00-20EP	NS	026526	160 (72.7)
18	240	3	44.7	120	3	1/4	1,725	1400 (2379)	1000 (304.8)	39 (21.7)	43 (13.1)	10 (3.0)	CXH-A-18-23-32-00-20EP	NS	026534	171 (77.7)
18	240	3	44.7	24	3	1/4	1,725	1400 (2379)	1000 (304.8)	39 (21.7)	43 (13.1)	10 (3.0)	CXH-A-18-23-30-00-20EP	NS	026542	171 (77.7)
20	480	3	24.8	120	3	1/4	1,725	1400 (2379)	1000 (304.8)	43 (23.9)	43 (13.1)	10 (3.0)	<b>CXH-A-20-43-32-00-20EP</b>	<b>S</b>	<b>025110</b>	171 (77.7)
20	575	3	20.7	120	3	1/4	1,725	1400 (2379)	1000 (304.8)	43 (23.9)	43 (13.1)	10 (3.0)	CXH-A-20-63-32-00-20EP	NS	026550	171 (77.7)
20	480	3	24.8	24	3	1/4	1,725	1400 (2379)	1000 (304.8)	43 (23.9)	43 (13.1)	10 (3.0)	CXH-A-20-43-30-00-20EP	NS	026569	171 (77.7)
20	575	3	20.7	24	3	1/4	1,725	1400 (2379)	1000 (304.8)	43 (23.9)	43 (13.1)	10 (3.0)	CXH-A-20-63-30-00-20EP	NS	026577	171 (77.7)
25	480	3	31.1	120	3	1/2	1,725	2330 (3959)	1070 (326.1)	32 (17.8)	54 (16.5)	10 (3.0)	CXH-A-25-43-32-00-20EP	NS	028556	216 (98.2)
25	575	3	25.8	120	3	1/2	1,725	2330 (3959)	1070 (326.1)	32 (17.8)	54 (16.5)	10 (3.0)	CXH-A-25-63-32-00-20EP	NS	028589	216 (98.2)
25	480	3	31.1	24	3	1/2	1,725	2330 (3959)	1070 (326.1)	32 (17.8)	54 (16.5)	10 (3.0)	CXH-A-25-43-30-00-20EP	NS	028602	216 (98.2)
25	575	3	25.8	24	3	1/2	1,725	2330 (3959)	1070 (326.1)	32 (17.8)	54 (16.5)	10 (3.0)	CXH-A-25-63-30-00-20EP	NS	028609	216 (98.2)
30	480	3	37.1	120	3	1/2	1,725	2330 (3959)	1070 (326.1)	39 (21.7)	54 (16.5)	10 (3.0)	<b>CXH-A-30-43-32-00-20EP</b>	<b>S</b>	<b>028564</b>	216 (98.2)
30	575	3	30.2	120	3	1/2	1,725	2330 (3959)	1070 (326.1)	39 (21.7)	54 (16.5)	10 (3.0)	CXH-A-30-63-32-00-20EP	NS	028615	216 (98.2)
30	480	3	37.1	24	3	1/2	1,725	2330 (3959)	1070 (326.1)	39 (21.7)	54 (16.5)	10 (3.0)	CXH-A-30-43-30-00-20EP	NS	028620	216 (98.2)
30	575	3	30.2	24	3	1/2	1,725	2330 (3959)	1070 (326.1)	39 (21.7)	54 (16.5)	10 (3.0)	CXH-A-30-63-30-00-20EP	NS	028625	216 (98.2)
35	480	3	43.1	120	3	1/2	1,725	2330 (3959)	1070 (326.1)	45 (25.0)	54 (16.5)	10 (3.0)	CXH-A-35-43-32-00-20EP	NS	028572	216 (98.2)
35	575	3	36	120	3	1/2	1,725	2330 (3959)	1070 (326.1)	45 (25.0)	54 (16.5)	10 (3.0)	CXH-A-35-63-32-00-20EP	NS	028605	216 (98.2)
35	480	3	43.1	24	3	1/2	1,725	2330 (3959)	1070 (326.1)	45 (25.0)	54 (16.5)	10 (3.0)	CXH-A-35-43-30-00-20EP	NS	028612	216 (98.2)
35	575	3	36	24	3	1/2	1,725	2330 (3959)	1070 (326.1)	45 (25.0)	54 (16.5)	10 (3.0)	CXH-A-35-63-30-00-20EP	NS	028617	216 (98.2)
<b>Models with Built-In Thermostats</b>																
10	480	3	12.7	120	3	1/4	1,725	840 (1427)	1070 (326.1)	36 (20.0)	32 (9.8)	10 (3.0)	<b>CXH-A-10-43-32-40-20EP</b>	<b>S</b>	<b>028580</b>	150 (68.2)
20	480	3	24.8	120	3	1/4	1,725	1400 (2379)	1070 (326.1)	43 (23.9)	43 (13.1)	10 (3.0)	<b>CXH-A-20-43-32-40-20EP</b>	<b>S</b>	<b>028599</b>	161 (73.2)
25	480	3	31.1	120	3	1/2	1,725	2330 (3959)	1070 (326.1)	32 (17.8)	54 (16.5)	10 (3.0)	CXH-A-25-43-32-40-20EP	NS	028601	216 (98.2)
30	480	3	37.1	120	3	1/2	1,725	2330 (3959)	1070 (326.1)	39 (21.7)	54 (16.5)	10 (3.0)	<b>CXH-A-30-43-32-40-20EP</b>	<b>S</b>	<b>028610</b>	216 (98.2)
35	480	3	43.1	120	3	1/2	1,725	2330 (3959)	1070 (326.1)	45 (25.0)	54 (16.5)	10 (3.0)	<b>CXH-A-35-43-32-40-20EP</b>	<b>S</b>	<b>-</b>	216 (98.2)

**Stock Status:** S = stock NS = non-stock  
**To Order**—Specify model, PCN, kW, volts, phase and quantity.