

## SSR Series Power Controllers SSR, SSR1, SSR1P, SSR2, SSR3 & SSR3P *(cont'd.)*

### Ordering Information

Complete the model number using the matrix provided.

### In Stock

Model	PCN
SSR3P-1521	339477
SSR3P-2511	339452
SSR3P-2521	339485
SSR3P-4011	339450
SSR3P-4021	339493

MODEL	Three-Phase, 3-Leg, Phase Fired Solid State Relay with Heat Sink			
SSR3P	The SSR3P series are industrial three-phase 3-leg relays mounted on heat sinks for switching high current resistive and inductive loads. Chromalox SSR3P series offers the following standard features: 40°C Ambient Rating, phase-angle controlled soft-start, LED status indicator for line ON and load ON, two input ranges, varistor protection, DIN rail mount, CE mark, UL and CSA approvals.			
	CODE	Current @ 40°C (104°F) Ambient		
	15	15 Amp		
	25	25 Amp Fan Cooled (120 Vac Required for Fan)		
40	40 Amp Fan Cooled (120 Vac Required for Fan)			
	CODE	Voltage		
	1	120 - 230 Vac		
	2	277 - 480 Vac		
		CODE	Input Control Voltage	
		1	4 - 20 mA / 0-20 mA	
SSR3P	25	1	1	Typical Model Number

### Note:

SSR3P requires external power supply. See SSR Accessories Table below for additional options.

### SSR Accessories Table

SSR Series	PCN									
	15 Amps	25 Amps	30 Amps	35 Amps	40 Amps	45 Amps	50 Amps	65 Amps	70 Amps	75 Amps
SSR Thermstrate (Thermal Conductor)	0029-00640	0029-00640	0029-00640	0029-00640	0029-00640	0029-00640	0029-00640	0029-00640	0029-00640	0029-00640
SSR3P Power Supply	0081-10030	0081-10030			0081-10030					