

Heating Cable

SRF

Self-Regulating Freeze Protection *(cont'd.)*

Ordering Information

Output (W/Ft.)	Volts	Model	Stock	PCN	Wt./1000' (Lbs.)
Output at Rated Voltage					
3 @ 50°F	120	SRF 3-1C	S	386943	53
	208 - 277	SRF 3-2C	S	386951	53
5 @ 50°F	120	SRF 5-1C	S	386960	53
	208 - 277	SRF 5-2C	S	386978	53
8 @ 50°F	120	SRF 8-1C	S	386986	53
	208 - 277	SRF 8-2C	S	386994	53
With Optional Overcoat (CR)					
3 @ 50°F	120	SRF 3-1CR	S	386100	64
	208 - 277	SRF 3-2CR	S	386118	64
5 @ 50°F	120	SRF 5-1CR	S	386142	64
	208 - 277	SRF 5-2CR	S	386150	64
8 @ 50°F	120	SRF 8-1CR	S	386062	64
	208 - 277	SRF 8-2CR	S	386070	64

Accessories

Accessories		U Series	DL	EL
Power Connection	Heat trace to electrical service connection	UPC	RTPC	SSK
Splice & Tee		UMC	RTST	RT-RST
End Seal	For terminating cable	UES	RTES	RT-RES
Thermostat	Ambient air sensing thermostat	UAS	RTAS	THL/TXL
	Line sensing mechanical thermostat	UBC	RTBC	THR/TXR

General Application & Installation Accessories such as tape, pipe straps, warning labels, etc., refer to the U Series and DL & EL General Application Accessories page at the end of this section.

Ordering Information

To Order —
Complete the Model Number using the Matrix provided.

Model	Self-Regulating Medium Temperature			
SRF	Self-Regulating, Freeze Protection Heating Cable			
	Code	Output (W/Ft.)		
	3	Three		
	5	Five		
	8	Eight		
	Code	Voltage		
	1	120		
	2	208 - 277		
	Code	Braid and Overcoat Options		
	C	Standard tinned-copper metallic braid for additional protection and ground path		
	CR	TPR overjacket over braid for protection against certain inorganic chemical solutions		
SRF	5	-	1	C
				Typical Model Number