

RAK16-POE-B-SO



- 19`` patch panel surge protector for POE-B
- 32 ports
- In/Out front : RJ45
- Maintenance possible per port
- Secondary Protection
- UL497B

Electrical Characteristics		
Insertion loss		< 1 dB
Max. load current	IL	750 mA
Max. capacitance	C	< 25 pF (ligne ethernet)
CapacityMaximum	pF	<25
Telecom Discharge Current10/1000	kA	0,13
Telecom Total Discharge Current10/1000	kA	0,5
Telecom Discharge Current10/1000	kA	0,13
Telecom Discharge Current10/1000	kA	0,5
label.propertyGroup.INSTALLATION		
Operating TemperatureMin	°C	-40.0000
Operating TemperatureMax	°C	85.0000
Operating TemperatureMin	°F	-40.0000
Operating TemperatureMax	°F	85.0000
Operating Relative HumidityMax	%RH	95
Operating AltitudeMin	Ft	2000.0000
Operating AltitudeMax	Ft	6500.0000
Housing/Enclosure material		aluminum
Mounting		Rack mount
IP Environmental ratingIP		IP20
Installation Location		indoor
Product DimensionL	mm	483.0000
Product DimensionH	mm	89.0000
Product DimensionL	In	19.0200
Product DimensionH	In	3.5040
label.propertyGroup.MISCELLANEOUS		
Individual Pack		Yes
Storage TemperatureMin	°C	-40.0000
Storage TemperatureMax	°C	85.0000
Storage TemperatureMin	°F	-40.0000
Storage TemperatureMax	°F	85.0000
label.propertyGroup.INSTALLATION		
Cable type		Ethernet
Mechanical Characteristics		
Outdoor application		No
Part number		
6285		