

# TSP15M-S-48D3



- 1 Pair Protection
- Modes of Protection L-L,L-G
- Conduit Mounting
- Direct Transducer Mount
- Parallel or Series Connection Options

Electrical Characteristics		
VOLTS	(V)	48
WIRES		4W+GROUND
LINE CURRENT MAX	(A)	0.3
AMBIENT MIN	(C)	-55
AMBIENT MAX	(C)	+85
IN15 impulses 8/20µs	(kA)	10
IMAX8/20µs	(kA)	15
label.propertyGroup.INSTALLATION		
Operating Relative HumidityMax	%RH	Can be submerged
Operating AltitudeMin	Ft	2000.0000
Operating AltitudeMax	Ft	6500.0000
Housing/Enclosure material		Stainless Steel
Mounting		Side mount
Installation Location		Indoor / outdoor
Product DimensionL	mm	114.3000
Product DimensionH	mm	26.0000
Product DimensionW	mm	27.9400
Product DimensionL	In	4.5000
Product DimensionH	In	1.0000
Product DimensionW	In	1.1000
Product Weight	lbs	0.8000
label.propertyGroup.MISCELLANEOUS		
Individual Pack		Yes
Part number		
6339		