



## Guide-Rite Conduit & Box Support Fasteners



- Consult factory for pre-fab box assemblies.

- BMC3 plate is available to support multiple conduit runs.
- Guide-Rite™ Riveted assembly secures electrical boxes and conduit runs to beam flanges 1/8" to 1/2" thick.
- Provides support for conduit on either side of electrical box.
- Assemblies using BMC3 plate include center conduit clamp. Additional conduit clamps may be purchased separately.



BG\_S18-U\_



BG\_S18-U\_MC3

UPC/Part Number	Catalog Number	Conduit Size	Flange Thickness	Box Qty.
78101103583	<b>BG6-S18-U24 *</b>	3/8"	1/8" to 1/4"	25
78101103584	<b>BG6-S18-U58 *</b>	3/8"	5/16" to 1/2"	25
78101103579	<b>BG812-S18-U24</b>	1/2", 3/4"	1/8" to 1/4"	25
78101103580	<b>BG812-S18-U58</b>	1/2", 3/4"	5/16" to 1/2"	25
78101103581	<b>BG16-S18-U24</b>	1"	1/8" to 1/4"	25
78101103582	<b>BG16-S18-U58</b>	1"	5/16" to 1/2"	25

Patent #4958792

### With Multiple Conduit Plate

78205152813	<b>BG6-S18-U24-MC3 *</b>	3/8"	1/8" to 1/4"	25
78205152814	<b>BG6-S18-U58-MC3 *</b>	3/8"	5/16" to 1/2"	25
78205152815	<b>BG812-S18-U24-MC3</b>	1/2", 3/4"	1/8" to 1/4"	25
78205152816	<b>BG812-S18-U58-MC3</b>	1/2", 3/4"	5/16" to 1/2"	25
78205152817	<b>BG16-S18-U24-MC3</b>	1"	1/8" to 1/4"	25
78205152823	<b>BG16-S18-U58-MC3</b>	1"	5/16" to 1/2"	25

\* BG-6 will accept the following range  $\varnothing.420 - \varnothing.675$ : 14/2 thru 10/4 MC/AC cable and 5/16" or 3/8" flexible conduit

Read safety/installation instruction sheets in packages before use.