



## "Z" Purlin Hangers

- Compensates for angle of purlin lip.
- Allows for parallel conduit runs or vertical support drops.
- Riveted fasteners will rotate 360°.
- Maximum Purlin thickness of 3/32".



BF13



BF12

UPC/Part Number	Catalog Number	Description	Static Load Cap. Lbs.	Box Qty.
78101118345	<b>BF13</b>	With 1/4" Hole	100	100
78101118340	<b>BF12</b>	For "S" Hooks	100	100



**Guide-Rite™**  
Fastener  
BG Series



Push-Type  
BP Series

UPC/Part Number	Catalog Number	Conduit Size EMT & Rigid	Static Load Cap. Lbs.	Box Qty.
78101118445	<b>BG-6-F13 *</b>	3/8"	100	100
78101118520	<b>BG-8-12-F13</b>	1/2", 3/4"	100	100
78101118590	<b>BG-16-F13</b>	1"	100	100
78101118675	<b>BG-20-F13</b>	1 1/4"	100	100
78101119290	<b>BP-8-F13</b>	1/2" EMT	25	100
78101119390	<b>BP-12-F13</b>	3/4" EMT 1/2" IMC, Rigid	25	100
78101119480	<b>BP-16-F13</b>	1" EMT 3/4" IMC, Rigid	25	50

\* BG-6 will accept the following range  $\varnothing.420 - \varnothing.675$ :  
14/2 thru 10/4 MC/AC cable and 5/16" or 3/8" flexible conduit

Read safety/installation instruction sheets in packages before use.