

# Eaton 1084-SDLG

Catalog Number: 1084-SDLG

Eaton B-Line series wall mounted panel enclosure, 10" height, 4" length, 8" width, NEMA 4, Hinged cover, SDLG enclosure, Wall mount, Medium single door, Thru holes, optional external mounting feet, Carbon steel, Seamless poured in-place gasket

## General specifications



Product Name	Catalog Number
Eaton B-Line series wall mounted panel enclosure	1084-SDLG
	UPC
	799038545125

Product Length/Depth	Product Height
4 in	10 in

Product Width	Product Weight
8 in	8 lb

## Certifications

UL 50  
CSA C22.2.  
NEMA

## Product specifications

### Special features

1/4 turn latches

### Closure type

Hinged

### Finish color

Painted

### Color

RAL 7035 light gray

### Wall thickness

16 gauge, 16 gauge

### Material

Carbon steel

### Mounting method

Wall

### Country of origin

US

### Cover type

Hinged

### Mounting hole details

Thru holes, optional external mounting feet

### NEMA Rating

4

### Model

SDLG enclosure

### Style

Medium single door

## Resources

### Catalogs

[Disconnect Enclosure Catalog](#)

### Specifications and datasheets

[Eaton Specification Sheet - 1084-SDLG](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)