

# Eaton 12105-12CHCS

Catalog Number: 12105-12CHCS

Eaton B-Line series JIC panel enclosure, 12" height, 5" length, 10" width, NEMA 12, Hinged cover, 12CHC enclosure, Wall mount, Small single door, External mounting feet, Carbon steel, Seamless poured in-place gasket



## General specifications

|   |                      |
|---|----------------------|
| Product Name                            | Catalog Number       |
| Eaton B-Line series JIC panel enclosure | 12105-12CHCS         |
| UPC                                     | Product Length/Depth |
| 782051129465                            | 5 in                 |
| Product Height                          | Product Width        |
| 12 in                                   | 10 in                |
| Product Weight                          | Certifications       |
| 9.5 lb                                  | UL 508A              |
|   | CSA C22.2.           |
|   | NEMA                 |

## Material/finish

### Material

Carbon steel

### Wall thickness

16 gauge

### Finish color

Painted

### Color

ANSI 61 gray

## Model

### Style

Small single door

### Model

12CHC enclosure

### Cover type

Hinged

### Mounting method

Wall

### Mounting hole details

External mounting feet

### Closure type

Hinged

### Special features

Cont. piano hinge, panel mount,plated door clamps

## Standards

### NEMA Rating

12

### Country of origin

US

## Resources

### Catalogs

[Electrical Enclosure Catalog](#)

### Specifications and datasheets

[Eaton Specification Sheet - 12105-12CHCS](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)