

# Eaton 12126-4QT

Catalog Number: 12126-4QT

Eaton B-Line series JIC panel enclosure, 12" height, 6" length, 12" width, NEMA 4, Hinged cover, 4QT enclosure, Wall mount, Small single door, External mounting feet, Carbon steel, Seamless poured in-place gasket



## General specifications

Product Name	Catalog Number
Eaton B-Line series JIC panel enclosure	12126-4QT
UPC	Product Length/Depth
782051881820	6 in
Product Height	Product Width
12 in	12 in
Product Weight	Certifications
11.6 lb	UL 50
	CSA C22.2.
	NEMA

## Material/finish

### Material

Carbon steel

### Wall thickness

16 gauge

### Finish color

Painted

### Color

ANSI 61 gray

## Model

### Style

Small single door

### Model

4QT enclosure

### Cover type

Hinged

### Mounting method

Wall

### Mounting hole details

External mounting feet

### Closure type

Hinged

### Special features

Continuous piano hinge, panel mount, 1/4 turn latches

## Standards

### NEMA Rating

4

### Country of origin

US

## Resources

### Catalogs

[Electrical Enclosure Catalog](#)

### Specifications and datasheets

[Eaton Specification Sheet - 12126-4QT](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)