

# Eaton 12126-SDLG

Catalog Number: 12126-SDLG

Eaton B-Line series wall mounted panel enclosure, 12" height, 6" length, 12" width, NEMA 4, Hinged cover, SDLG enclosure, Wall mount, Medium single door, Thru holes, optional external mounting feet, Carbon steel, Seamless poured in-place gasket

## General specifications



|  |                       |
|--|-----------------------|
| <b>Product Name</b>                              | <b>Catalog Number</b> |
| Eaton B-Line series wall mounted panel enclosure | 12126-SDLG            |
|  | <b>UPC</b>            |
|  | 799038545156          |
| <b>Product Length/Depth</b>                      | <b>Product Height</b> |
| 6 in   | 12 in                 |
| <b>Product Width</b>                             | <b>Product Weight</b> |
| 12 in  | 13.7 lb               |

## Certifications

UL 50  
CSA C22.2.  
NEMA

## Product specifications

### Special features

1/4 turn latches

### Closure type

Hinged

### Finish color

Painted

### Color

RAL 7035 light gray

### Wall thickness

16 gauge, 16 gauge

### Material

Carbon steel

### Mounting method

Wall

### Country of origin

US

### Cover type

Hinged

### Mounting hole details

Thru holes, optional external mounting feet

### NEMA Rating

4

### Model

SDLG enclosure

### Style

Medium single door

## Resources

### Catalogs

[Disconnect Enclosure Catalog](#)

### Specifications and datasheets

[Eaton Specification Sheet - 12126-SDLG](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)