

# Eaton 201610-SDLG

Catalog Number: 201610-SDLG

Eaton B-Line series wall mounted panel enclosure,20" height,10" length,16" width,NEMA 4,Hinged cover,SDLG enclosure,Wall mount,Medium single door,Thru holes,optional external mounting feet,Carbon steel,Seamless poured in-place gasket

## General specifications



Product Name	Catalog Number
Eaton B-Line series wall mounted panel enclosure	201610-SDLG
	UPC
	799038545439

Product Length/Depth	Product Height
10 in	20 in

Product Width	Product Weight
16 in	29.8 lb

## Certifications

UL 50  
CSA C22.2.  
NEMA

## Product specifications

### Special features

1/4 turn latches

### Closure type

Hinged

### Finish color

Painted

### Color

RAL 7035 light gray

### Wall thickness

16 gauge, 16 gauge

### Material

Carbon steel

### Mounting method

Wall

### Country of origin

US

### Cover type

Hinged

### Mounting hole details

Thru holes, optional external mounting feet

### NEMA Rating

4

### Model

SDLG enclosure

### Style

Medium single door

## Resources

### Catalogs

[Disconnect Enclosure Catalog](#)

### Specifications and datasheets

[Eaton Specification Sheet - 201610-SDLG](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)