

# Eaton 201610-SDSS6

Catalog Number: 201610-SDSS6

Eaton B-Line series wall mounted panel enclosure,20" height,10" length,16" width,NEMA 4X,Hinged cover,SDSS6 enclosure,Wall mount,Medium single door,Thru holes,opt. external mounting feet,316 stainless steel,Seamless poured in-place gasket

## General specifications



Product Name	Catalog Number
Eaton B-Line series wall mounted panel enclosure	201610-SDSS6
	UPC
	799038654445

Product Length/Depth	Product Height
10 in	20 in

Product Width	Product Weight
16 in	23.6 lb

## Certifications

UL 50  
CSA C22.2.  
NEMA

## Product specifications

### Special features

Stainless 1/4 turn latches

### Closure type

Hinged

### Finish color

#4 brushed

### Color

Gray

### Wall thickness

16 gauge, 16 gauge

### Material

316 stainless steel

### Mounting method

Wall

### Country of origin

US

### Cover type

Hinged

### Mounting hole details

Thru holes, optional external mounting feet

### NEMA Rating

4X

### Model

SDSS6 enclosure

### Style

Medium single door

## Resources

### Catalogs

[Disconnect Enclosure Catalog](#)

### Specifications and datasheets

[Eaton Specification Sheet - 201610-SDSS6](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)