

Eaton 20206-SDLG

Catalog Number: 20206-SDLG

Eaton B-Line series wall mounted panel enclosure,20" height,6" length,20" width,NEMA 4,Hinged cover,SDLG enclosure,Wall mount,Medium single door,Thru holes,optional external mounting feet,Carbon steel,Seamless poured in-place gasket

General specifications



Product Name	Catalog Number
Eaton B-Line series wall mounted panel enclosure	20206-SDLG
	UPC
	799038545200

Product Length/Depth	Product Height
6 in	20 in

Product Width	Product Weight
20 in	30.1 lb

Certifications

UL 50
CSA C22.2.
NEMA

Product specifications

Special features

1/4 turn latches

Closure type

Hinged

Finish color

Painted

Color

RAL 7035 light gray

Wall thickness

16 gauge, 16 gauge

Material

Carbon steel

Mounting method

Wall

Country of origin

US

Cover type

Hinged

Mounting hole details

Thru holes, optional external mounting feet

NEMA Rating

4

Model

SDLG enclosure

Style

Medium single door

Resources

Catalogs

[Disconnect Enclosure Catalog](#)

Specifications and datasheets

[Eaton Specification Sheet - 20206-SDLG](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)