

Eaton 24208-43PT

Catalog Number: 24208-43PT

Eaton B-Line series wall mounted panel enclosure, 24" height, 8" length, 20" width, NEMA 4, Hinged cover, 43PT enclosure, Wall mount, Medium single door, External mounting feet, Carbon steel, Seamless poured in-place gasket



General specifications

Product Name	Catalog Number
Eaton B-Line series wall mounted panel enclosure	24208-43PT
	UPC
	782051883398
Product Length/Depth	Product Height
8 in	24 in
Product Width	Product Weight
20 in	39.4 lb

Certifications

UL 50
CSA C22.2.
NEMA

Product specifications

Special features

3-pt latching handle

Closure type

Hinged

Finish color

Painted

Color

ANSI 61 gray

Wall thickness

16 gauge

Material

Carbon steel

Mounting method

Wall

Country of origin

US

Cover type

Hinged

Mounting hole details

External mounting feet

Locking provisions

Key lock padlock provision

NEMA Rating

4

Model

43PT enclosure

Style

Medium single door

Resources

Catalogs

[Disconnect Enclosure Catalog](#)

Specifications and datasheets

[Eaton Specification Sheet - 24208-43PT](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)