

# Eaton 242412-43PT

Catalog Number: 242412-43PT

Eaton B-Line series wall mounted panel enclosure, 24" height, 12" length, 24" width, NEMA 4, Hinged cover, 43PT enclosure, Wall mount, Medium single door, External mounting feet, Carbon steel, Seamless poured in-place gasket



## General specifications

Product Name	Catalog Number
Eaton B-Line series wall mounted panel enclosure	242412-43PT
	UPC
	782051883497
Product Length/Depth	Product Height
12 in	24 in
Product Width	Product Weight
24 in	58.7 lb

## Certifications

UL 50  
CSA C22.2.  
NEMA

## Product specifications

### Special features

3-pt latching handle

### Closure type

Hinged

### Finish color

Painted

### Color

ANSI 61 gray

### Wall thickness

14 gauge

### Material

Carbon steel

### Mounting method

Wall

### Country of origin

US

### Cover type

Hinged

### Mounting hole details

External mounting feet

### Locking provisions

Key lock padlock provision

### NEMA Rating

4

### Model

43PT enclosure

### Style

Medium single door

## Resources

### Catalogs

[Disconnect Enclosure Catalog](#)

### Specifications and datasheets

[Eaton Specification Sheet - 242412-43PT](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)