

# Eaton 242412-4XS3PT

Catalog Number: 242412-4XS3PT

Eaton B-Line series wall mounted panel enclosure, 24" height, 12" length, 24" width, NEMA 4X, Hinged cover, 4XS3PT enclosure, Wall mount, Medium single door, External mounting feet, 304 stainless steel, Seamless poured in-place gasket



## General specifications

Product Name	Catalog Number
Eaton B-Line series wall mounted panel enclosure	242412-4XS3PT
	UPC
	782051883992

Product Length/Depth	Product Height
12 in	24 in

Product Width	Product Weight
24 in	59.5 lb

## Certifications

UL 508A  
CSA C22.2.  
NEMA

## Product specifications

### Special features

3-pt latching handle

### Closure type

Hinged

### Finish color

#4 brushed

### Color

Gray

### Wall thickness

14 gauge

### Material

304 stainless steel

### Mounting method

Wall

### Country of origin

US

### Cover type

Hinged

### Mounting hole details

External mounting feet

### Locking provisions

Key lock padlock provision

### NEMA Rating

4X

### Model

4XS3PT enclosure

### Style

Medium single door

## Resources

### Catalogs

[Disconnect Enclosure Catalog](#)

### Specifications and datasheets

[Eaton Specification Sheet - 242412-4XS3PT](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)