

Eaton 24428-4XSD3PT

Catalog Number: 24428-4XSD3PT

Eaton B-Line series wall mounted panel enclosure, 24" height, 8" length, 42" width, NEMA 4X, Hinged cover, 4XSD3PT enclosure, Wall mount, Medium double door, External mounting feet, 304 stainless steel, Seamless poured in-place gasket

General specifications



Product Name	Catalog Number
Eaton B-Line series wall mounted panel enclosure	24428-4XSD3PT
	UPC
	782051885521

Product Length/Depth	Product Height
8 in	24 in

Product Width	Product Weight
42 in	85.9 lb

Certifications

UL 508A
CSA C22.2.
NEMA

Product specifications

Special features

Stainless handle with 3-pt latching

Closure type

Hinged

Finish color

#4 brushed

Color

Gray

Wall thickness

14 gauge

Material

304 stainless steel

Mounting method

Wall

Country of origin

US

Cover type

Hinged

Mounting hole details

External mounting feet

Locking provisions

Key lock padlock provision

NEMA Rating

4X

Model

4XSD3PT enclosure

Style

Medium double door

Resources

Catalogs

[Disconnect Enclosure Catalog](#)

Specifications and datasheets

[Eaton Specification Sheet - 24428-4XSD3PT](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)