

Eaton 363612-4XS3PT

Catalog Number: 363612-4XS3PT

Eaton B-Line series wall mounted panel enclosure, 36" height, 12" length, 36" width, NEMA 4X, Hinged cover, 4XS3PT enclosure, Wall mount, Medium single door, External mounting feet, 304 stainless steel, Seamless poured in-place gasket



General specifications

Product Name	Catalog Number
Eaton B-Line series wall mounted panel enclosure	363612-4XS3PT
	UPC
	782051884036
Product Length/Depth	Product Height
12 in	36 in
Product Width	Product Weight
36 in	106.5 lb
Certifications	
UL 508A	
CSA C22.2.	
NEMA	

Product specifications

Special features

3-pt latching handle

Closure type

Hinged

Finish color

#4 brushed

Color

Gray

Wall thickness

14 gauge

Material

304 stainless steel

Mounting method

Wall

Country of origin

US

Cover type

Hinged

Mounting hole details

External mounting feet

Locking provisions

Key lock padlock provision

NEMA Rating

4X

Model

4XS3PT enclosure

Style

Medium single door

Resources

Catalogs

[Disconnect Enclosure Catalog](#)

Specifications and datasheets

[Eaton Specification Sheet - 363612-4XS3PT](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)