

Eaton 722418-4FS3PT

Catalog Number: 722418-4FS3PT

Eaton B-Line series ground mounted panel enclosure, 72" height, 18" length, 24" width, NEMA 4, Hinged cover, 4FS3PT enclosure, Ground mount, Large single door, No mounting provisions, Carbon steel, Seamless poured in-place gasket



General specifications

Product Name	Catalog Number
Eaton B-Line series type 4 panel enclosures	722418-4FS3PT
	UPC
	782051891171
Product Length/Depth	Product Height
18 in	72 in
Product Width	Product Weight
24 in	254 lb
Certifications	
UL 50	
CSA C22.2.	
NEMA	

Material/finish

Material

Carbon steel

Wall thickness

12 gauge

Finish color

Painted

Color

ANSI 61 gray

Model

Style

Large single door

Model

4FS3PT enclosure

Cover type

Hinged

Mounting method

Ground

Mounting hole details

No mounting provisions

Locking provisions

Key lock padlock provision

Closure type

Hinged

Special features

3-pt latching handle

Standards

NEMA Rating

4

Country of origin

US

Resources

Catalogs

[Electrical Enclosure Catalog](#)

Specifications and datasheets

[Eaton Specification Sheet - 722418-4FS3PT](#)