

Eaton 722424-4XSFS3PT

Catalog Number: 722424-4XSFS3PT

Eaton B-Line series ground mounted panel enclosure, 72" height, 24" length, 24" width, NEMA 4X, Hinged cover, 4XSFS3PT enclosure, Ground mount, Large single door, No mounting provisions, 304 stainless steel, Seamless poured in-place gasket



General specifications

| | |
|----------------------------------------------|-----------------------|
| Product Name | Catalog Number |
| Eaton B-Line series type 4X panel enclosures | 722424-4XSFS3PT |
| | UPC |
| | 782051892154 |
| Product Length/Depth | Product Height |
| 24 in | 72 in |
| Product Width | Product Weight |
| 24 in | 375.9 lb |
| Certifications | |
| UL 50 | |
| CSA C22.2. | |
| NEMA | |

Material/finish

Material

304 stainless steel

Wall thickness

12 gauge

Finish color

#4 brushed

Color

Gray

Model

Style

Large single door

Model

4XSFS3PT enclosure

Cover type

Hinged

Mounting method

Ground

Mounting hole details

No mounting provisions

Locking provisions

Key lock padlock provision

Closure type

Hinged

Special features

3-pt latching handle

Standards

NEMA Rating

4X

Country of origin

US

Resources

Catalogs

[Electrical Enclosure Catalog](#)

Specifications and datasheets

[Eaton Specification Sheet - 722424-4XSFS3PT](#)