

Eaton 723024-4XSFSQT

Catalog Number: 723024-4XSFSQT

Eaton B-Line series ground mounted panel enclosure, 72" height, 24" length, 30" width, NEMA 4X, Hinged cover, 4XSFSQT enclosure, Ground mount, Large single door, Ground mount legs, 304 stainless steel, Seamless poured in-place gasket



General specifications

Product Name	Catalog Number
Eaton B-Line series type 4X panel enclosures	723024-4XSFSQT
	UPC
	782051894882
Product Length/Depth	Product Height
24 in	72 in
Product Width	Product Weight
30 in	324.3 lb
Certifications	
UL 50	
CSA C22.2.	
NEMA	

Material/finish

Material

304 stainless steel

Wall thickness

12 gauge, 14 gauge

Finish color

#4 brushed

Color

Gray

Model

Style

Large single door

Model

4XSFSQT enclosure

Cover type

Hinged

Mounting method

Ground

Mounting hole details

Ground mount legs

Locking provisions

Padlock provision

Closure type

Hinged

Special features

1/4 turn latches

Standards

NEMA Rating

4X

Country of origin

US

Resources

Catalogs

[Electrical Enclosure Catalog](#)

Specifications and datasheets

[Eaton Specification Sheet - 723024-4XSFSQT](#)