

# Eaton 723624-4FS3PT

Catalog Number: 723624-4FS3PT

Eaton B-Line series ground mounted panel enclosure, 72" height, 24" length, 36" width, NEMA 4, Hinged cover, 4FS3PT enclosure, Ground mount, Large single door, No mounting provisions, Carbon steel, Seamless poured in-place gasket



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton B-Line series type 4 panel enclosures	723624-4FS3PT
	<b>UPC</b>
	782051891232
<b>Product Length/Depth</b>	<b>Product Height</b>
24 in	72 in
<b>Product Width</b>	<b>Product Weight</b>
36 in	363.7 lb
<b>Certifications</b>	
UL 50	
CSA C22.2.	
NEMA	

## Material/finish

### Material

Carbon steel

### Wall thickness

12 gauge

### Finish color

Painted

### Color

ANSI 61 gray

## Model

### Style

Large single door

### Model

4FS3PT enclosure

### Cover type

Hinged

### Mounting method

Ground

### Mounting hole details

No mounting provisions

### Locking provisions

Key lock padlock provision

### Closure type

Hinged

### Special features

3-pt latching handle

## Standards

### NEMA Rating

4

### Country of origin

US

## Resources

### Catalogs

[Electrical Enclosure Catalog](#)

### Specifications and datasheets

[Eaton Specification Sheet - 723624-4FS3PT](#)